



LED Lamps

LEDBulb 19W B22 6500K 230VA80 1CT/6APR

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | B22 |
| Nominal lifetime | 12,000 hour(s) |
| Switching Cycle | 50,000 |
| Rated Lifetime (Hours) | 12,000 hour(s) |
| Lighting Technology | LED |
| Light Technical | |
| Color Code | 865 [CCT of 6500K] |
| Beam Angle (Nom) | 150 degree(s) |
| Luminous Flux | 2,300 lm |
| Luminous Efficacy (rated) (Nom) | 121 lm/W |
| Color Designation | Cool Daylight |
| Correlated Color Temperature (Nom) | 6500 K |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 19 W |
| Lamp Current (Nom) | 170 mA |
| Wattage Equivalent | 160 W |

| Starting Time (Nom) | 0.5 s |
|-------------------------------|---------------|
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.51 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| Ambient temperature range | -20 to +45 °C |
| T-Case Maximum (Nom) | 90 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Material | Plastic |
| Bulb Shape | A80 |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 19 kWh |
| EU RoHS compliant | Yes |
| EyeComfort | No |


LEDLamps

Product Data

| | |
|-------------------------------|--|
| Order product name | LEDBulb 19W B22 6500K 230VA80 1CT/6APR |
| Full product name | LEDBulb 19W B22 6500K 230VA80 1CT/6APR |
| Full product code | 871869964061300 |
| Order code | 929002004749 |
| Material Nr. (12NC) | 929002004749 |
| Numerator - Quantity Per Pack | 1 |

| | |
|---------------------------------|---------------|
| Net Weight (Piece) | 0.147 kg |
| EAN/UPC - Product/Case | 8718699640613 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8718699640620 |


Dimensional drawing




Product

LEDBulb 19W B22 6500K 230VA80 1CT/6APR


Photometric data



Spectral Power Distribution Colour - LEDBulb 19W B22 6500K 230VA80 1CT/6APR



Light Distribution Diagram - LEDBulb 19W B22 6500K 230VA80 1CT/6APR




General uniform lighting - LEDBulb 19W B22 6500K 230VA80 1CT/6APR

General uniform lighting - LEDBulb 19W B22 6500K 230VA80 1CT/6APR

LEDLamps

Lifetime



Lumen Maintenance Diagram - LEDBulb 19W B22 6500K 230VA80 1CT/
6APR

Life Expectancy Diagram

