



LEDLamps

LEDBulb 19W B22 6500K 230VA80 1CT/6APR

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost


Product data

General Information		Starting Time (Nom)		0.5 s
Cap-Base	B22	Warm-up time to 60% light		0.5 s
Nominal lifetime	12,000 hour(s)	Power Factor (Fraction)		0.51
Switching Cycle	50,000	Voltage (Nom)		220-240 V
Rated Lifetime (Hours)	12,000 hour(s)	Temperature		
Lighting Technology	LED	Ambient temperature range		-20 to +45 °C
Light Technical		T-Case Maximum (Nom)		90 °C
Color Code	865 [CCT of 6500K]	Controls and Dimming		
Beam Angle (Nom)	150 degree(s)	Dimmable		No
Luminous Flux	2,300 lm	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	121 lm/W	Bulb Finish		Frosted
Color Designation	Cool Daylight	Bulb Material		Plastic
Correlated Color Temperature (Nom)	6500 K	Bulb Shape		A80
Color Consistency	<6	Approval and Application		
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h		19 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	EU RoHS compliant		Yes
Operating and Electrical		EyeComfort		No
Input Frequency	50 to 60 Hz			
Power Consumption	19 W			
Lamp Current (Nom)	170 mA			
Wattage Equivalent	160 W			

Product Data	
Order product name	LEDBulb 19W B22 6500K 230VA80 1CT/6APR
Full product name	LEDBulb 19W B22 6500K 230VA80 1CT/6APR
Full product code	871869964061300
Order code	929002004749
Material Nr. (12NC)	929002004749
Numerator - Quantity Per Pack	1


Net Weight (Piece)	0.147 kg
EAN/UPC - Product/Case	8718699640613
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699640620

Dimensional drawing




Product
LEDBulb 19W B22 6500K 230VA80 1CT/6APR


Photometric data



Spectral Power Distribution Colour - LEDBulb 19W B22 6500K 230VA80 1CT/6APR




Light Distribution Diagram - LEDBulb 19W B22 6500K 230VA80 1CT/6APR




General uniform lighting - LEDBulb 19W B22 6500K 230VA80 1CT/6APR

Lifetime



Lumen Maintenance Diagram - LEDBulb 19W B22 6500K 230VA80 1CT/6APR



Life Expectancy Diagram

