

Standard LED bulbs

LEDBulb 9W E27 6500K W 1PF/40 BR

LEDbulb, A60, 60 W, E27, 6500 K, 806 lm, 25000 hour(s), Plastic

LEDbulb, A60, 60 W, E27, 6500 K, 806 lm, 25000 hour(s), Plastic, 90 lm/W

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Warranty period	2 years

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	806 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	9 W
Lamp Current (Nom)	77 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	100-240 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	10.8 mm
Overall width	6 mm
Overall height	10.8 mm
Dimensions (Height x Width x Depth)	11 x 6 x 11 mm
Bulb Shape	A60

Standard LED bulbs

Net Weight (Piece)	0.038 kg

Approval and Application

EU RoHS compliant	Yes
EyeComfort	No
Ambient temperature range	-20 °C to 45 °C


Application Conditions

Wireless Technology	Not applicable

Product Data


Order product name	LEDBulb 9W E27 6500K W 1PF/40 BR
Full product name	LEDBulb 9W E27 6500K W 1PF/40 BR
Full product code	871869965591400
Order code	929002038012
Material Nr. (12NC)	929002038012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699655914
Numerator - Packs per outer box	40
EAN/UPC - Case	8718699655921

Dimensional drawing




Product	D	C
LEDBulb 9W E27 6500K W 1PF/40 BR	60 mm	108 mm

Photometric data




General uniform lighting - LEDBulb 9W E27 6500K W 1PF/40 BR



Light Distribution Diagram - LEDBulb 9W E27 6500K W 1PF/40 BR


Standard LED bulbs

Photometric data




Spectral Power Distribution Colour - LEDBulb 9W E27 6500K W 1PF/40 BR

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 9W E27 6500K W 1PF/40 BR

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.