



# Classic filament LEDbulbs

## LED classic 150W A67 E27 WW CL ND 1SRT4

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Flux measurement reference	Sphere
Light Technical	
Colour Code	827 [CCT of 2700K]
Colour Code	827 [CCT of 2700K]
Luminous Flux	2,452 lm
Luminous efficacy (rated) (nom.)	144.00 lm/W
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1

Stroboscopic effect	0.4
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	17 W
Lamp current (nom.)	140 mA
Wattage equivalent	150 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	60 °C
Controls and Dimming	
Dimmable	No

# Classic filament LEDbulbs

## Mechanical and Housing

Lamp Finish	Clear
Bulb material	Glass
Bulb shape	A67

## Approval and Application

Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	17 kWh
EPREL registration number	374867
EU RoHS compliant	Yes
EyeComfort	Yes
LED innovations	EyeComfort


## Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

## Product Data



Order product name	LED classic 150W A67 E27 WW CL ND 1SRT4
Full product name	LED classic 150W A67 E27 WW CL ND 1SRT4
Full EOC	871869976237700
Order code	76237700
Material no. (12 NC)	929002055055
Numerator – quantity per pack	1
Net Weight (Piece)	0.034 kg
EAN/UPC – Product/Case	8718699762377
Numerator – packs per outer box	4
EAN/UPC - Case	8718699762384

## Dimensional drawing



Product	D	C
LED classic 150W A67 E27 WW CL ND 1SRT4	70 mm	128 mm

## Photometric data




General uniform lighting - LED classic 150W A67 E27 WW CL ND 1SRT4

Light Distribution Diagram - LED classic 150W A67 E27 WW CL ND 1SRT4


# Classic filament LEDbulbs

## Photometric data




Spectral Power Distribution Colour - LED classic 150W A67 E27 WW CL ND 1SRT4

## Lifetime



Lumen Maintenance Diagram - LED classic 150W A67 E27 WW CL ND 1SRT4



Life Expectancy Diagram

