



LED 3-Way

14A21/LED/927/P/E26/3WAY ND 4/1FB T20

Philips LED A-shape light bulb provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	25,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	250 degree(s)
Luminous Efficacy (rated) (Nom)	114.00 lm/W
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	14.5 8 W
Lamp Current (Max)	120 mA
Lamp Current (Min)	38 mA

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A21
UL Wet/ damp/ dry location	Damp location
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort

LED 3-Way

Application Conditions


can it be used in closed luminaires No

Product Data

Order product name	14A21/LED/927/P/E26/3WAY ND 4/1FB T20
Full product name	14A21/LED/927/P/E26/3WAY ND 4/1FB T20
Order code	556944
Material Nr. (12NC)	929002285005



Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.096 kg
EAN/UPC - Product/Case	046677556945
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677556940

Dimensional drawing




Product	D	C
14A21/LED/927/P/E26/3WAY ND 4/1FB T20	70.6 mm	133.1 mm

Photometric data



General uniform lighting - 14A21/LED/927/P/E26/3WAY ND 4/1FB T20

Light Distribution Diagram - 14A21/LED/927/P/E26/3WAY ND 4/1FB T20



Spectral Power Distribution Colour - 14A21/LED/927/P/E26/3WAY ND 4/1FB T20

LED 3-Way

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 14A21/LED/927/P/E26/3WAY ND 4/1FB T20

