



Specialty Lamps

18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

General Information		Operating and Electrical	
Cap-Base	E26D [3 Contact Medium Screw]	Input Frequency	60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	18.5 13 6 W
Switching Cycle	50,000	Lamp Current (Max)	157 mA
Rated Lifetime (Hours)	15,000 hour(s)	Lamp Current (Min)	54 mA
Lighting Technology	LED	Wattage Equivalent	150 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	927 [CCT of 2700K]	Warm-up time to 60% light	0.5 s
Color Code	927 [CCT of 2700K]	Power Factor (Fraction)	0.7
Beam Angle (Nom)	250 degree(s)	Voltage (Nom)	120 V
Luminous Flux	2,150 1,600 620 lm	Temperature	
Color Designation	Warm White (WW)	Ambient temperature range	-4 to +113 °F
Luminous Efficacy (rated) (Nom)	116 lm/W	T-Case Maximum (Nom)	203 °F
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Color Consistency	<4	Dimmable	No
Color rendering index (CRI)	90	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted

Specialty Lamps

Bulb Material	Plastic
Bulb Shape	A21
UL Wet/ damp/ dry location	Damp location

Approval and Application


EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort

Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----



Product Data	
Order product name	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF
Full product name	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF
Order code	571521
Material Nr. (12NC)	929002285133
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.331 lb
EAN/UPC - Product/Case	046677571528
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677571523

Dimensional drawing



Product	D	C
18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	2-13/16 inch	5-1/4 inch

Photometric data




General uniform lighting - 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF

Light Distribution Diagram - 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF


Specialty Lamps

Photometric data




Spectral Power Distribution Colour - 18.5A21/PER/927/FR/P/
E26/3WAY/T20 4/1PF

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 18.5A21/PER/927/FR/P/E26/3WAY/T20
4/1PF

