



A-Shape LED

9A19/LED/827/FR/P/ND 4/6FB

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	11,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Color Code	827 [CCT of 2700K]
Luminous Flux	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	88.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	9 W
Lamp Current (Nom)	165 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	85 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19 [A 19mm]

Approval and Application	
Energy Consumption kWh/1000 h	9 kWh
EyeComfort	Yes


Product Data	
Order product name	9A19/LED/827/FR/P/ND 4/6FB
Full product name	9A19/LED/827/FR/P/ND 4/6FB
Order code	455592

A-Shape LED

Material Nr. (12NC)	929002311375
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677455590
Numerator - Packs per outer box	4



EAN/UPC - Case	50046677455595
----------------	----------------

Dimensional drawing




Product	D	C
9A19/LED/827/FR/P/ND 4/6FB	60 mm	104 mm

Photometric data



Light Distribution Diagram - 9A19/LED/827/FR/P/ND 4/6FB

Spectral Power Distribution Colour - 9A19/LED/827/FR/P/ND 4/6FB





© 2023 Philips Lighting B.V. Page 11

General uniform lighting - 9A19/LED/827/FR/P/ND 4/6FB

A-Shape LED

Lifetime



Life Expectancy Diagram - 9A19/LED/827/FR/P/ND 4/6FB

Lumen Maintenance Diagram - 9A19/LED/827/FR/P/ND 4/6FB

