



BR/R LED

15BR30/PER/927/P/E26/WG/HO/T20 4/1PF

Philips Dimmable LED Reflector Lamps provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.7
Switching Cycle	50,000	Voltage (Nom)		120 V
Rated Lifetime (Hours)	15,000 hour(s)			
Lighting Technology	LED	Temperature		
Light Technical		Ambient temperature range		-4 to +113 °F
Color Code	922-927 [CCT of 2200K-2700K]	T-Case Maximum (Nom)		203 °F
Color Code	922-927 [CCT of 2200K-2700K]	Controls and Dimming		
Beam Angle (Nom)	110 degree(s)	Dimmable		Only with specific dimmers
Luminous Flux	1,400 lm	Mechanical and Housing		
Color Designation	Warm Glow(WG)	Bulb Finish		Frosted
Luminous Efficacy (rated) (Nom)	93 lm/W	Bulb Material		Plastic
Correlated Color Temperature (Nom)	2200 2700 K	Bulb Shape		BR30
Color Consistency	<4	UL Wet/ damp/ dry location		Damp location
Color rendering index (CRI)	90	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	EU RoHS compliant		Yes
Operating and Electrical		EyeComfort		Yes
Input Frequency	60 Hz	T20 compliant		Yes
Power Consumption	15 W	LED Innovations		EyeComfort
Lamp Current (Nom)	125 mA			
Wattage Equivalent	100 W			

BR/R LED

Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	15BR30/PER/927/P/E26/WG/HO/T20 4/1PF
Full product name	15BR30/PER/927/P/E26/WG/HO/T20 4/1PF
Order code	571471
Material Nr. (12NC)	929002351433



Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.159 lb
EAN/UPC - Product/Case	046677571474
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677571479

Dimensional drawing




Product	D	C
15BR30/PER/927/P/E26/WG/HO/T20 4/1PF	3-3/4 inch	5-1/8 inch

Photometric data



Light Distribution Diagram - 15BR30/PER/927/P/E26/WG/HO/T20 4/1PF

General uniform lighting - 15BR30/PER/927/P/E26/WG/HO/T20 4/1PF



Spectral Power Distribution Colour - 15BR30/PER/927/P/E26/WG/HO/T20 4/1PF

