

Ecofit Ledtubes T8

Ledtube DE 1200mm 16W 765 T8 G13

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	G13	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.5
Switching Cycle	50,000	Voltage (Nom)		220-240 V
Lighting Technology	LED	Ballast Compatibility		EM/Mains
Light Technical		Temperature		
Color Code	765 [CCT of 6500K]	Ambient temperature range		-20 to +45 °C
Beam Angle (Nom)	240 degree(s)	T-Case Maximum (Nom)		55 °C
Luminous Flux	1,600 lm	Controls and Dimming		
Luminous Efficacy (rated) (Nom)	100 lm/W	Dimmable		No
Color Designation	Cool Daylight	Mechanical and Housing		
Correlated Color Temperature (Nom)	6500 K	Bulb Finish		Frosted
Color Consistency	<7	Bulb Material		Glass
Color rendering index (CRI)	70	Product Length		1,200 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape		T8
Operating and Electrical		Approval and Application		
Input Frequency	50 to 60 Hz	Energy Saving Product		Yes
Power Consumption	16 W	Approval Marks		RoHS compliance
Lamp Current (Nom)	130 mA			
Wattage Equivalent	36 W			

Ecofit Ledtubes T8

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Product Data	
Order product name	Ledtube DE 1200mm 16W 765 T8 G13
Full product name	Ledtube DE 1200mm 16W 765 T8 G13
Full product code	871869975489100
Order code	929002351968


Material Nr. (12NC)	929002351968
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.225 kg
EAN/UPC - Product/Case	8718699754891
Numerator - Packs per outer box	20
EAN/UPC - Case	8718699754907

Dimensional drawing




Product	D1	D2	A1	A2	A3
Ledtube DE 1200mm 16W 765 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm


Photometric data



Spectral Power Distribution Colour - Ledtube DE 1200mm 16W 765 T8 G13




Light Distribution Diagram - Ledtube DE 1200mm 16W 765 T8 G13




General uniform lighting - Ledtube DE 1200mm 16W 765 T8 G13

Ecofit Ledtubes T8


Lifetime




Life Expectancy Diagram



Life Expectancy Diagram



Lumen Maintenance Diagram - Ledtube DE 1200mm 16W 765 T8 G13



Lumen Maintenance Diagram - Ledtube DE 1200mm 16W 765 T8 G13

Life Expectancy Diagram

Ecofit Ledtubes T8

