



Classic filament LEDbulbs

LEDclassic 11W A60 E27 smoky ND RFSRT4

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	818 [CCT of 1800K]
Colour Code	818 [CCT of 1800K]
Luminous Flux	100 lm
Colour designation	1800
Correlated Colour Temperature	1800 K
Luminous efficacy (rated) (nom.)	43 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4

Photobiological safety according to EN 62471 RG1	
Photobiological safety according to EN 62471 RG1	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	2.3 W
Lamp current (nom.)	21 mA
Wattage equivalent	11 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.54
Voltage (nom.)	220-240 V
Temperature	
Ambient temperature range	-20 to +40 °C
T-Case maximum (nom.)	40 °C
Controls and Dimming	
Dimmable	No

Classic filament LEDbulbs

Mechanical and Housing

Lamp Finish	smoky
Bulb material	Glass
Bulb shape	A60 [A 60 mm]

Approval and Application


Energy consumption kWh/1,000 hours	3 kWh
EyeComfort	Yes

Product Data

Order product name	LEDclassic 11W A60 E27 smoky ND RFSRT4
--------------------	---


Full product name	LEDclassic 11W A60 E27 smoky ND RFSRT4
Full EOC	871869975963600
Order code	75963600
Material no. (12 NC)	929002380501
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699759636
Numerator – packs per outer box	4
EAN/UPC – Case	8718699759643

Dimensional drawing




Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm

Photometric data




Spectral Power Distribution Colour - LEDclassic 11W A60 E27 smoky ND RFSRT4



Light Distribution Diagram - LEDclassic 11W A60 E27 smoky ND RFSRT4

Classic filament LEDbulbs

Photometric data



General uniform lighting - LEDclassic 11W A60 E27 smoky ND RFSRT4

Lifetime



Life Expectancy Diagram - LEDclassic 11W A60 E27 smoky ND RFSRT4



Lumen Maintenance Diagram - LEDclassic 11W A60 E27 smoky ND RFSRT4

