



Classic filament LEDbulbs

LEDclassic 11W ST64 E27 smoky ND RFSRT4

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	818 [CCT of 1800K]
Colour Code	818 [CCT of 1800K]
Luminous Flux	100 lm
Colour designation	1800
Correlated Colour Temperature	1800 K
Luminous efficacy (rated) (nom.)	43 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4

Photobiological safety according to EN 62471 RG1	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	2.3 W
Lamp current (nom.)	21 mA
Wattage equivalent	11 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.54
Voltage (nom.)	220-240 V
Temperature	
Ambient temperature range	-20 to +40 °C
T-Case maximum (nom.)	40 °C
Controls and Dimming	
Dimmable	No

Classic filament LEDbulbs

Mechanical and Housing

Lamp Finish	smoky
Bulb material	Glass
Bulb shape	ST64

Approval and Application


Energy consumption kWh/1,000 hours	3 kWh
EyeComfort	Yes

Product Data

Order product name	LEDclassic 11W ST64 E27 smoky ND RFSRT4
--------------------	--


Full product name	LEDclassic 11W ST64 E27 smoky ND RFSRT4
Full EOC	871869975965000
Order code	75965000
Material no. (12 NC)	929002380601
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699759650
Numerator – packs per outer box	4
EAN/UPC – Case	8718699759667

Dimensional drawing




Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm

Photometric data




Spectral Power Distribution Colour - LEDclassic 11W ST64 E27 smoky ND RFSRT4



Light Distribution Diagram - LEDclassic 11W ST64 E27 smoky ND RFSRT4


Classic filament LEDbulbs

Photometric data



General uniform lighting - LEDclassic 11W ST64 E27 smoky ND RFSRT4

Lifetime



Life Expectancy Diagram - LEDclassic 11W ST64 E27 smoky ND RFSRT4

Lumen Maintenance Diagram - LEDclassic 11W ST64 E27 smoky ND RFSRT4

