



Classic filament LEDbulbs

LED classic 25W ST64 E27 pink D SRT4

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	818 [CCT of 1800K]
Colour Code	818 [CCT of 1800K]
Luminous Flux	250 lm
Colour designation	1800
Correlated Colour Temperature	1800 K
Luminous efficacy (rated) (nom.)	55.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4

Photobiological safety according to EN 62471		RG1
Operating and Electrical		
Line Frequency	50 to 60 Hz	
Input frequency	50 to 60 Hz	
Power Consumption	4.5 W	
Lamp current (nom.)	26 mA	
Wattage equivalent	25 W	
Starting time (nom.)	0.5 s	
Warm-up time to 60% light	0.5 s	
Power Factor (Fraction)	0.5	
Voltage (nom.)	220-240 V	
Temperature		
T-Case maximum (nom.)	40 °C	
Controls and Dimming		
Dimmable	Yes	

Classic filament LEDbulbs

Mechanical and Housing

Lamp Finish	Pink
Bulb shape	ST19

Approval and Application


Energy consumption kWh/1,000 hours	5 kWh
EyeComfort	Yes

Product Data

Order product name	LED classic 25W ST64 E27 pink D SRT4
--------------------	--------------------------------------



Full product name	LED classic 25W ST64 E27 pink D SRT4
Full EOC	871951426953800
Order code	26953800
Material no. (12 NC)	929002453701
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514269538
Numerator – packs per outer box	4
EAN/UPC – Case	8719514269545

Dimensional drawing



Product	D	C
LED classic 25W ST64 E27 pink D SRT4	64 mm	140 mm

Photometric data




Light Distribution Diagram - LED classic 25W ST64 E27 pink D SRT4

General uniform lighting - LED classic 25W ST64 E27 pink D SRT4

Classic filament LEDbulbs

Photometric data




Spectral Power Distribution Colour - LED classic 25W ST64 E27 pink D SRT4

Lifetime



Life Expectancy Diagram - LED classic 25W ST64 E27 pink D SRT4



Lumen Maintenance Diagram - LED classic 25W ST64 E27 pink D SRT4

