

Classic filament LEDbulbs

LED classic 25W G93 E27 pink D 1PF/4

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

| General Information | |
|--|--------------------|
| Cap base | E27 [E27] |
| Nominal lifetime | 15,000 h |
| Switching Cycle | 20,000 |
| Rated Lifetime (Hours) | 15,000 h |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Colour Code | 818 [CCT of 1800K] |
| Colour Code | 818 [CCT of 1800K] |
| Luminous Flux | 250 lm |
| Colour designation | 1800 |
| Correlated Colour Temperature | 1800 K |
| Luminous efficacy (rated) (nom.) | 55.00 lm/W |
| Colour consistency | <6 |
| Colour rendering index (CRI) | 80 |
| LLMF at end of nominal lifetime (nom.) | 70 % |
| Flickering value (PstLM) | 1 |
| Stroboscopic effect | 0.4 |

| Photobiological safety according to EN 62471 | RG1 |
|--|-------------|
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input frequency | 50 to 60 Hz |
| Power Consumption | 4.5 W |
| Lamp current (nom.) | 26 mA |
| Wattage equivalent | 25 W |
| Starting time (nom.) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.5 |
| Voltage (nom.) | 220-240 V |
| Temperature | |
| T-Case maximum (nom.) | 40 °C |
| Controls and Dimming | |
| Dimmable | Yes |

Classic filament LEDbulbs

Mechanical and Housing

| | |
|-------------|---------------|
| Lamp Finish | Pink |
| Bulb shape | G93 [G 93 mm] |

Approval and Application


| | |
|------------------------------------|-------|
| Energy consumption kWh/1,000 hours | 5 kWh |
| EyeComfort | Yes |

Product Data

| | |
|--------------------|--------------------------------------|
| Order product name | LED classic 25W G93 E27 pink D 1PF/4 |
|--------------------|--------------------------------------|



| | |
|-----------------------------------|--------------------------------------|
| Full product name | LED classic 25W G93 E27 pink D 1PF/4 |
| Full EOC | 871951426955200 |
| Order code | 26955200 |
| Material no. (12 NC) | 929002453801 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8719514269552 |
| Numerator – packs per outer box | 4 |
| EAN/UPC – Case | 8719514269569 |

Dimensional drawing



| Product | D | C |
|--------------------------------------|-------|--------|
| LED classic 25W G93 E27 pink D 1PF/4 | 95 mm | 140 mm |

Photometric data




Spectral Power Distribution Colour - LED classic 25W G93 E27 pink D 1PF/4

General uniform lighting - LED classic 25W G93 E27 pink D 1PF/4

Classic filament LEDbulbs

Photometric data



Light Distribution Diagram - LED classic 25W G93 E27 pink D 1PF/4

Lifetime



Life Expectancy Diagram - LED classic 25W G93 E27 pink D 1PF/4



Lumen Maintenance Diagram - LED classic 25W G93 E27 pink D 1PF/4

