




Classic filament LEDbulbs

LED classic 25W G93 E27 pink D 1PF/4

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	818 [CCT of 1800K]
Color Code	818 [CCT of 1800K]
Luminous Flux	250 lm
Color Designation	1800
Correlated Color Temperature (Nom)	1800 K
Luminous Efficacy (rated) (Nom)	55.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4


Photobiological safety according to EN 62471		RG1
Operating and Electrical		
Line Frequency	50 to 60 Hz	
Input Frequency	50 to 60 Hz	
Power Consumption	4.5 W	
Lamp Current (Nom)	26 mA	
Wattage Equivalent	25 W	
Starting Time (Nom)	0.5 s	
Warm-up time to 60% light	0.5 s	
Power Factor (Fraction)	0.5	
Voltage (Nom)	220–240 V	
Temperature		
T-Case Maximum (Nom)	40 °C	
Controls and Dimming		
Dimmable	Yes	

Classic filament LEDbulbs

Mechanical and Housing	
Bulb Finish	Pink
Bulb Shape	G93 [G 93mm]
Approval and Application	
Energy Consumption kWh/1000 h	5 kWh
EyeComfort	Yes
Product Data	
Order product name	LED classic 25W G93 E27 pink D 1PF/4


Full product name	LED classic 25W G93 E27 pink D 1P/4
Full product code	871951426955200
Order code	929002453801
Material Nr. (12NC)	929002453801
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514269552
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514269569

Dimensional drawing




Product	D	C
LED classic 25W G93 E27 pink D 1PF/4	95 mm	140 mm

Photometric data




Spectral Power Distribution Colour - LED classic 25W G93 E27 pink D 1PF/4



General uniform lighting - LED classic 25W G93 E27 pink D 1PF/4

Classic filament LEDbulbs

Photometric data




Light Distribution Diagram - LED classic 25W G93 E27 pink D 1PF/4

Lifetime



Life Expectancy Diagram - LED classic 25W G93 E27 pink D 1PF/4



Lumen Maintenance Diagram - LED classic 25W G93 E27 pink D 1PF/4

