



# Classic filament LEDbulbs

## LED classic 25W ST64 E27 gradient D SRT

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Colour Code	818 [CCT of 1800K]
Colour Code	818 [CCT of 1800K]
Luminous Flux	250 lm
Luminous efficacy (rated) (nom.)	55.00 lm/W
Colour designation	1800
Correlated Colour Temperature	1800 K
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4

Photobiological safety according to EN 62471 RG1	
Photobiological safety according to EN 62471 RG1	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	4.5 W
Lamp current (nom.)	26 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	40 °C
Controls and Dimming	
Dimmable	Yes

# Classic filament LEDbulbs

## Mechanical and Housing

Lamp Finish	Amber Gradient
Bulb material	Glass
Bulb shape	ST19

## Approval and Application

Energy consumption kWh/1,000 hours	5 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED innovations	EyeComfort


## Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

## Product Data


Order product name	LED classic 25W ST64 E27 gradient D SRT
Full product name	LED classic 25W ST64 E27 gradient D SRT
Full EOC	871951426959000
Order code	26959000
Material no. (12 NC)	929002454001
Numerator – quantity per pack	1
Net Weight (Piece)	0.042 kg
EAN/UPC – Product/Case	8719514269590
Numerator – packs per outer box	4
EAN/UPC - Case	8719514269606

## Dimensional drawing




Product	D	C
LED classic 25W ST64 E27 gradient D SRT	64 mm	140 mm

## Photometric data




Spectral Power Distribution Colour - LED classic 25W ST64 E27 gradient D SRT



Light Distribution Diagram - LED classic 25W ST64 E27 gradient D SRT

# Classic filament LEDbulbs

## Photometric data



General uniform lighting - LED classic 25W ST64 E27 gradient D SRT

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED classic 25W ST64 E27 gradient D SRT

