



Candle LED

LEDCandle 5-40W E14 865 B35NDFR AU 2CT

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data


General Information		Wattage Equivalent	
Cap-Base	E14		40 W
Nominal lifetime	15,000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15,000 h	Power Factor (Fraction)	0.51
Lighting Technology	LED	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	865 [CCT of 6500K]	Ambient temperature range	-20 to +45 °C
Color Code	865 [CCT of 6500K]	T-Case Maximum (Nom)	81 °C
Luminous Flux	470 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Luminous Efficacy (rated) (Nom)	94 lm/W	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Bulb Finish	Frosted
Color Consistency	<6	Bulb Material	Plastic
Color rendering index (CRI)	80	Bulb Shape	B35
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Photobiological safety according to EN 62471	RG1	Energy Consumption kWh/1000 h	- kWh
Operating and Electrical		EU RoHS compliant	Yes
Input Frequency	50 to 60 Hz	EyeComfort	Yes
Power Consumption	5 W		
Lamp Current (Nom)	44 mA		

Candle LED

LED Innovations	EyeComfort
Product Data	
Order product name	LEDCandle 5-40W E14 865 B35NDFR AU 2CT
Full product name	LEDCandle 5-40W E14 865 B35NDFR AU 2CT
Full product code	871951432251600
Order code	929002969279



Material Nr. (12NC)	929002969279
Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.021 kg
EAN/UPC - Product/Case	8719514322516
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514322523

Dimensional drawing




Product	D	C
LEDCandle 5-40W E14 865 B35NDFR AU 2CT	35 mm	106 mm

Photometric data



Spectral Power Distribution Colour - LEDCandle 5-40W E14 865 B35NDFR AU 2CT



General uniform lighting - LEDCandle 5-40W E14 865 B35NDFR AU 2CT



Light Distribution Diagram - LEDCandle 5-40W E14 865 B35NDFR AU 2CT

Candle LED

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDCandle 5-40W E14 865 B35NDFR AU 2CT

