



Classic filament LEDbulbs

LED giant 20W E27 G200 1800K smoky D

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	818 [CCT of 1800K]
Color Code	818 [CCT of 1800K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	200 lm
Luminous Efficacy (rated) (Nom)	30 lm/W
Color Designation	1800
Correlated Color Temperature (Nom)	1800 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4


Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	20 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	Only with specific dimmers

Classic filament LEDbulbs

Mechanical and Housing	
Bulb Finish	smoky
Bulb Material	Glass
Bulb Shape	G200
Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Application Conditions	
can it be used in closed luminaires	No


Product Data	
Order product name	LED giant 20W E27 G200 1800K smoky D
Full product name	LED giant 20W E27 G200 1800K smoky D
Full product code	871951431539600
Order code	929002982601
Material Nr. (12NC)	929002982601
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.360 kg
EAN/UPC - Product/Case	8719514315396
Numerator - Packs per outer box	2
EAN/UPC - Case	8719514315402

Dimensional drawing




Product	D	C
LED giant 20W E27 G200 1800K smoky D	202 mm	286 mm

Photometric data




Light Distribution Diagram - LED giant 20W E27 G200 1800K smoky D



Spectral Power Distribution Colour - LED giant 20W E27 G200 1800K smoky D

Classic filament LEDbulbs



Photometric data



Catalytic Performance 4.5	Philips Lighting B.V.	Page 17
---------------------------	-----------------------	---------

General uniform lighting - LED giant 20W E27 G200 1800K smoky D

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LED giant 20W E27 G200 1800K smoky D

