



# Classic filament LEDbulbs

## LED classic 25W G93 E27 GOLD SP D SRT4

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Colour Code	818 [CCT of 1800K]
Colour Code	818 [CCT of 1800K]
Beam angle (nom.)	330 degree(s)
Luminous Flux	250 lm
Luminous efficacy (rated) (nom.)	62 lm/W
Colour designation	1800
Correlated Colour Temperature	1800 K
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4

Photobiological safety according to EN 62471 RG1	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	4 W
Lamp current (nom.)	24 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case maximum (nom.)	35 °C
Controls and Dimming	
Dimmable	Only with specific dimmers

# Classic filament LEDbulbs

## Mechanical and Housing

Lamp Finish	Amber
Bulb material	Glass
Bulb shape	G93

## Approval and Application

Energy consumption kWh/1,000 hours	4 kWh
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
LED innovations	EyeComfort


## Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

## Product Data



Order product name	LED classic 25W G93 E27 GOLD SP D SRT4
Full product name	LED classic 25W G93 E27 GOLD SP D SRT4
Full EOC	871951431547100
Order code	31547100
Material no. (12 NC)	929002983001
SAP numerator – quantity per pack	1
Net Weight (Piece)	0.060 kg
EAN/UPC – Product/Case	8719514315471
Numerator – packs per outer box	4
EAN/UPC - Case	8719514315488

## Dimensional drawing



Product	D	C
LED classic 25W G93 E27 GOLD SP D SRT4	96 mm	143 mm

## Photometric data




Light Distribution Diagram – LED classic 25W G93 E27 GOLD SP D SRT4

General uniform lighting – LED classic 25W G93 E27 GOLD SP D SRT4

# Classic filament LEDbulbs

## Photometric data




Spectral Power Distribution Colour - LED classic 25W G93 E27 GOLD SP D SRT4

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED classic 25W G93 E27 GOLD SP D SRT4

