



# LED A15

## 5A15/PER/UD/CL/G/E26/WGD 6/2PF T20

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED

Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	450 lm
Color Designation	Warm Glow(WG)
Luminous Efficacy (rated) (Nom)	90 lm/W
Correlated Color Temperature (Nom)	2200 2700 K
Color Consistency	<4
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5 W
Lamp Current (Nom)	55 mA

Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.4 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
Ambient temperature range	-4 °F to 104 °F

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A15
UL Wet/ damp/ dry location	Wet location


Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort

LED A15

Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	5A15/PER/UD/CL/G/E26/WGD 6/2PF T20
Full product name	5A15/PER/UD/CL/G/E26/WGD 6/2PF T20
Order code	564385
Material Nr. (12NC)	929002986503


Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.053 lb
EAN/UPC - Product/Case	046677564384
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677564389

Dimensional drawing




Product	D	C
5A15/PER/UD/CL/G/E26/WGD 6/2PF T20	1-7/8 inch	3-5/16 inch


Photometric data



General uniform lighting - 5A15/PER/UD/CL/G/E26/WGD 6/2PF T20




Spectral Power Distribution Colour - 5A15/PER/UD/CL/G/E26/WGD 6/2PF T20




Light Distribution Diagram - 5A15/PER/UD/CL/G/E26/WGD 6/2PF T20

LED A15

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5A15/PER/UD/CL/G/E26/WGD 6/2PF T20

