

# Classic filament LED candles and lusters

## 6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	Universal
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	700 lm
Color Designation	Warm Glow(WG)
Luminous Efficacy (rated) (Nom)	106 lm/W
Correlated Color Temperature (Nom)	2200 2700 K
Color Consistency	<4
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	0.7 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	6.6 W
Lamp Current (Nom)	65 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.4 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
Ambient temperature range	-4 °F to 104 °F

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass

## Classic filament LED candles and lusters

Bulb Shape	BA11
UL Wet/ damp/ dry location	Wet location

### Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort

### Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

### Product Data

Order product name	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20
--------------------	---



Full product name	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20
Order code	564492
Material Nr. (12NC)	929002986603
Numerator - Quantity Per Pack	3
Net Weight (Piece)	0.044 lb
EAN/UPC - Product/Case	046677564490
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677564495

## Dimensional drawing



Product	D	C
6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	1-3/8 inch	4-1/4 inch

## Photometric data




Light Distribution Diagram - 6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20

General uniform lighting - 6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20


# Classic filament LED candles and lusters

## Photometric data




Spectral Power Distribution Colour - 6.6BA11/PER/UD/CL/G/E12+E26/WGD  
3PF T20

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF  
T20

