



A-Shape LED

11A19/LED/927/FR/P/E26/ND 4/2CT

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

| General Information | | Lamp Current (Nom) | |
|---------------------------------------|-----------------------------------|----------------------------|---------------|
| Cap-Base | E26 [Single Contact Medium Screw] | | 146 mA |
| Nominal lifetime | 11,000 hour(s) | Wattage Equivalent | 75 W |
| Switching Cycle | 50,000 | Starting Time (Nom) | 0.5 s |
| Rated Lifetime (Hours) | 11,000 hour(s) | Warm-up time to 60% light | 0.5 s |
| Lighting Technology | LED | Power Factor (Fraction) | 0.5 |
| EU RoHS compliant | Yes | Voltage (Nom) | 120 V |
| Light Technical | | Temperature | |
| Color Code | 927 [CCT of 2700K] | T-Case Maximum (Nom) | 203 °F |
| Color Code | 927 [CCT of 2700K] | Controls and Dimming | |
| Beam Angle (Nom) | 150 degree(s) | Dimmable | No |
| Luminous Flux | 1,000 lm | Mechanical and Housing | |
| Color Designation | Warm White (WW) | Bulb Finish | Frosted |
| Correlated Color Temperature (Nom) | 2700 K | Bulb Shape | A19 [A 19mm] |
| Luminous Efficacy (rated) (Nom) | 90.00 lm/W | UL Wet/ damp/ dry location | Damp location |
| Color Consistency | <6 | Approval and Application | |
| Color rendering index (CRI) | 90 | Energy Certifications | No |
| LLMF At End Of Nominal Lifetime (Nom) | 0.7 % | EyeComfort | Yes |
| Operating and Electrical | | T20 compliant | No |
| Line Frequency | 60 Hz | | |
| Input Frequency | 60 Hz | | |
| Power Consumption | 11 W | | |

A-Shape LED

Application Conditions


can it be used in closed luminaires Yes

Product Data

| | |
|--------------------|---------------------------------|
| Order product name | 11A19/LED/927/FR/P/E26/ND 4/2CT |
| Full product name | 11A19/LED/927/FR/P/E26/ND 4/2CT |
| Order code | 565366 |



| | |
|---------------------------------|----------------|
| Material Nr. (12NC) | 929003005103 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677565367 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 50046677565362 |

Dimensional drawing




| Product | D | C |
|---------------------------------|-------|--------|
| 11A19/LED/927/FR/P/E26/ND 4/2CT | 60 mm | 106 mm |

Photometric data



Light Distribution Diagram - 11A19/LED/927/FR/P/E26/ND 4/2CT



Spectral Power Distribution Colour - 11A19/LED/927/FR/P/E26/ND 4/2CT



General uniform lighting - 11A19/LED/927/FR/P/E26/ND 4/2CT

A-Shape LED

Lifetime



Lumen Maintenance Diagram - 11A19/LED/927/FR/P/E26/ND 4/2CT

Life Expectancy Diagram - 11A19/LED/927/FR/P/E26/ND 4/2CT

