



A-Shape LED

10A19/LED/950/FR/P/E26/ND 4/2CT

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information		Lamp Current (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]		146 mA
Nominal lifetime	11,000 hour(s)	Wattage Equivalent	75 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	11,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.5
EU RoHS compliant	Yes	Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	950 [CCT of 5000K]	T-Case Maximum (Nom)	203 °F
Color Code	950 [CCT of 5000K]	Controls and Dimming	
Beam Angle (Nom)	150 degree(s)	Dimmable	No
Luminous Flux	1,000 lm	Mechanical and Housing	
Color Designation	Daylight	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	5000 K	Bulb Shape	A19 [A 19mm]
Luminous Efficacy (rated) (Nom)	100.00 lm/W	UL Wet/ damp/ dry location	Damp location
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	90	Energy Certifications	No
LLMF At End Of Nominal Lifetime (Nom)	0.7 %	EyeComfort	Yes
Operating and Electrical		T20 compliant	No
Line Frequency	60 Hz		
Input Frequency	60 Hz		
Power Consumption	10 W		

A-Shape LED

Application Conditions

can it be used in closed luminaires Yes

Product Data

Order product name	10A19/LED/950/FR/P/E26/ND 4/2CT
Full product name	10A19/LED/950/FR/P/E26/ND 4/2CT
Order code	565382

Material Nr. (12NC) 929003005303


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 046677565381

Numerator - Packs per outer box 4



EAN/UPC - Case 50046677565386

Dimensional drawing




Product	D	C
10A19/LED/950/FR/P/E26/ND 4/2CT	60 mm	106 mm

Photometric data



Spectral Power Distribution Colour - 10A19/LED/950/FR/P/E26/ND 4/2CT



Light Distribution Diagram - 10A19/LED/950/FR/P/E26/ND 4/2CT



General uniform lighting - 10A19/LED/950/FR/P/E26/ND 4/2CT

A-Shape LED

Lifetime



Lumen Maintenance Diagram - 10A19/LED/950/FR/P/E26/ND 4/2CT

Life Expectancy Diagram - 10A19/LED/950/FR/P/E26/ND 4/2CT

