



A-Shape LED

14A19/LED/927/FR/P/E26/ND 4/2CT

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Lamp Current (Nom)		223 mA
Cap-Base	E26 [Single Contact Medium Screw]	Wattage Equivalent		100 W
Nominal lifetime	11,000 hour(s)	Starting Time (Nom)		0.5 s
Switching Cycle	50,000	Warm-up time to 60% light		0.5 s
Rated Lifetime (Hours)	11,000 hour(s)	Power Factor (Fraction)		0.5
Lighting Technology	LED	Voltage (Nom)		120 V
EU RoHS compliant	Yes			
Light Technical		Temperature		
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)		203 °F
Color Code	927 [CCT of 2700K]			
Beam Angle (Nom)	150 degree(s)	Controls and Dimming		
Luminous Flux	1,500 lm	Dimmable		No
Color Designation	Warm White (WW)			
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	107.00 lm/W	Bulb Finish		Frosted
Color Consistency	<6	Bulb Shape		A19 [A 19mm]
Color rendering index (CRI)	90	UL Wet/ damp/ dry location		Damp location
LLMF At End Of Nominal Lifetime (Nom)	0.7 %			
Operating and Electrical		Approval and Application		
Line Frequency	60 Hz	Energy Certifications		No
Input Frequency	60 Hz	EyeComfort		Yes
Power Consumption	14 W	T20 compliant		No

A-Shape LED

Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	14A19/LED/927/FR/P/E26/ND 4/2CT
Full product name	14A19/LED/927/FR/P/E26/ND 4/2CT
Order code	565507



Material Nr. (12NC)	929003005403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565503
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565508

Dimensional drawing




Product	D	C
14A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	117 mm

Photometric data



General uniform lighting - 14A19/LED/927/FR/P/E26/ND 4/2CT


Spectral Power Distribution Colour - 14A19/LED/927/FR/P/E26/ND 4/2CT




Light Distribution Diagram - 14A19/LED/927/FR/P/E26/ND 4/2CT

A-Shape LED

Lifetime



Lumen Maintenance Diagram - 14A19/LED/927/FR/P/E26/ND 4/2CT



Life Expectancy Diagram - 14A19/LED/927/FR/P/E26/ND 4/2CT

