



Classic filament LEDbulbs

LEDclassic 60W A60 2700K E27 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED

Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Lamp Current (Nom)	40 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A60
Net Weight (Piece)	0.034 kg


Approval and Application	
Energy Consumption kWh/1000 h	6 kWh
EU RoHS compliant	Yes
EyeComfort	Yes

Classic filament LEDbulbs

LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LEDclassic 60W A60 2700K E27 D CL AU
Full product name	LEDclassic 60W A60 2700K E27 D CL AU
Full product code	87195143771200
Order code	929003010379


Material Nr. (12NC)	929003010379
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514377172
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377189

Dimensional drawing




Product	D	C
LEDclassic 60W A60 2700K E27 D CL AU	60 mm	104 mm


Photometric data



Spectral Power Distribution Colour - LEDclassic 60W A60 2700K E27 D CL AU



Light Distribution Diagram - LEDclassic 60W A60 2700K E27 D CL AU



General uniform lighting - LEDclassic 60W A60 2700K E27 D CL AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDclassic 60W A60 2700K E27 D CL AU

