



Classic filament LEDbulbs

LEDclassic 60W A60 2700K E27 D CL AU

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Luminous Flux	806 lm
Luminous Efficacy (rated) (Nom)	134 lm/W
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power Consumption	6 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A60

Classic filament LEDbulbs

Approval and Application


Energy Consumption kWh/1000 h	6 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Product Data

Order product name	LEDclassic 60W A60 2700K E27 D CL AU
Full product name	LEDclassic 60W A60 2700K E27 D CL AU
Full product code	87195143771200


Order code	929003010379
Material Nr. (12NC)	929003010379
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.034 kg
EAN/UPC - Product/Case	8719514377172
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377189

Dimensional drawing




Product	D	C
LEDclassic 60W A60 2700K E27 D CL AU	60 mm	104 mm

Photometric data




Spectral Power Distribution Colour - LEDclassic 60W A60 2700K E27 D CL AU



Light Distribution Diagram - LEDclassic 60W A60 2700K E27 D CL AU

Classic filament LEDbulbs

Photometric data




General uniform lighting - LEDclassic 60W A60 2700K E27 D CL AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 60W A60 2700K E27 D CL AU

