



Classic filament LEDbulbs

LEDclassic 60W ST64 2700K B22 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Wattage Equivalent	
Cap-Base	B22	60 W	
Nominal lifetime	15,000 h	Starting Time (Nom)	
Switching Cycle	20,000	0.5 s	
Rated Lifetime (Hours)	15,000 h	Warm-up time to 60% light	
Lighting Technology	LED	0.5 s	
Light Technical		Power Factor (Fraction)	
Color Code	927 [CCT of 2700K]	0.6	
Color Code	927 [CCT of 2700K]	Voltage (Nom)	
Luminous Flux	806 lm	220-240 V	
Color Designation	Warm White (WW)	Temperature	
Luminous Efficacy (rated) (Nom)	134 lm/W	Ambient temperature range	
Correlated Color Temperature (Nom)	2700 K	-20 to +45 °C	
Color Consistency	<6	T-Case Maximum (Nom)	
Color rendering index (CRI)	90	70 °C	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Controls and Dimming	
Operating and Electrical		Dimmable	
Input Frequency	50 to 60 Hz	Only with specific dimmers	
Power Consumption	6 W	Mechanical and Housing	
Lamp Current (Nom)	40 mA	Bulb Finish	
		Clear	
		Bulb Material	
		Glass	
		Bulb Shape	
		ST64	
		Approval and Application	
		Energy Consumption kWh/1000 h	
		6 kWh	
		EU RoHS compliant	
		Yes	
		EyeComfort	
		Yes	

Classic filament LEDbulbs

LED Innovations	EyeComfort
Product Data	
Order product name	LEDclassic 60W ST64 2700K B22 D CL AU
Full product name	LEDclassic 60W ST64 2700K B22 D CL AU
Full product code	871951437723300
Local code description	FIL60WST64WWBCD
Order code	929003010879
Material Nr. (12NC)	929003010879


Local order code	FIL60WST64WWBCD
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.048 kg
EAN/UPC - Product/Case	8719514377233
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377240

Dimensional drawing




Product	D	C
LEDclassic 60W ST64 2700K B22 D CL AU	64 mm	139 mm


Photometric data



Spectral Power Distribution Colour - LEDclassic 60W ST64 2700K B22 D CL AU




Light Distribution Diagram - LEDclassic 60W ST64 2700K B22 D CL AU



General uniform lighting - LEDclassic 60W ST64 2700K B22 D CL AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDclassic 60W ST64 2700K B22 D CL AU

