



Classic filament LED candles and lusters

LEDclassic 40W B35 2700K E14 D CL AU

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E14 |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 20,000 |
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Lighting Technology | LED |
| Light Technical | |
| Color Code | 927 [CCT of 2700K] |
| Color Code | 927 [CCT of 2700K] |
| Luminous Flux | 470 lm |
| Luminous Efficacy (rated) (Nom) | 134 lm/W |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Color Consistency | <6 |
| Color rendering index (CRI) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |

| Power Consumption | 3.5 W |
|---------------------------|----------------------------|
| Lamp Current (Nom) | 24 mA |
| Wattage Equivalent | 40 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.6 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| Ambient temperature range | -20 to +45 °C |
| T-Case Maximum (Nom) | 70 °C |
| Controls and Dimming | |
| Dimmable | Only with specific dimmers |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Material | Glass |
| Bulb Shape | B35 |

Classic filament LED candles and lusters

Approval and Application


| | |
|-------------------------------|------------|
| Energy Consumption kWh/1000 h | 4 kWh |
| EU RoHS compliant | Yes |
| EyeComfort | Yes |
| LED Innovations | EyeComfort |

Product Data

| | |
|--------------------|--------------------------------------|
| Order product name | LEDclassic 40W B35 2700K E14 D CL AU |
| Full product name | LEDclassic 40W B35 2700K E14 D CL AU |
| Full product code | 871951437729500 |


| | |
|---------------------------------|---------------|
| Order code | 929003012279 |
| Material Nr. (12NC) | 929003012279 |
| Numerator - Quantity Per Pack | 1 |
| Net Weight (Piece) | 0.014 kg |
| EAN/UPC - Product/Case | 8719514377295 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8719514377301 |

Dimensional drawing




| Product | D | C |
|--------------------------------------|-------|-------|
| LEDclassic 40W B35 2700K E14 D CL AU | 35 mm | 97 mm |

Photometric data




Light Distribution Diagram - LEDclassic 40W B35 2700K E14 D CL AU



Spectral Power Distribution Colour - LEDclassic 40W B35 2700K E14 D CL AU

Classic filament LED candles and lusters

Photometric data



General uniform lighting - LEDclassic 40W B35 2700K E14 D CL AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 40W B35 2700K E14 D CL AU

