



Classic filament LED candles and lusters

LEDclassic 40W B35 2700K B22 ND FR AU

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	B22
Nominal lifetime	15,000 h
Switching Cycle	15,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	134 lm/W
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz


Power Consumption	3.5 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	B35

Classic filament LED candles and lusters

Approval and Application	
Energy Consumption kWh/1000 h	4 kWh
EU RoHS compliant	Yes
EyeComfort	No
Product Data	
Order product name	LEDclassic 40W B35 2700K B22 ND FR AU
Full product name	LEDclassic 40W B35 2700K B22 ND FR AU
Full product code	871951437737000



Order code	929003012879
Material Nr. (12NC)	929003012879
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.014 kg
EAN/UPC - Product/Case	8719514377370
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377387

Dimensional drawing



Product	D	C
LEDclassic 40W B35 2700K B22 ND FR AU	35 mm	94 mm

Photometric data




General uniform lighting - LEDclassic 40W B35 2700K B22 ND FR AU

Spectral Power Distribution Colour - LEDclassic 40W B35 2700K B22 ND FR AU

Classic filament LED candles and lusters

Photometric data




Light Distribution Diagram - LEDclassic 40W B35 2700K B22 ND FR AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 40W B35 2700K B22 ND FR AU

