



Classic filament LEDbulbs

LED CLA 40W A60 E27 3000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	50,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	50,000 h
Lighting Technology	LED

Light Technical	
Color Code	830 [CCT of 3000K]
Color Code	830 [CCT of 3000K]
Luminous Flux	485 lm
Color Designation	White (WH)
Luminous Efficacy (rated) (Nom)	210 lm/W
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	2.3 W

Lamp Current (Nom)	30 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	35 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A60


Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes

Classic filament LEDbulbs

EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Product Data	
Order product name	LED CLA 40W A60 E27 3000K CL EELA SRT AU
Full product name	LED CLA 40W A60 E27 3000K CL EELA SRT AU
Full product code	871951445493400



Order code	929003066419
Material Nr. (12NC)	929003066419
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.036 kg
EAN/UPC - Product/Case	8719514454934
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514454941

Dimensional drawing



Product	D	C
LED CLA 40W A60 E27 3000K CL EELA SRT AU	60 mm	105 mm

Photometric data




General Uniform Lighting 1 x STANDARD LIGHTING

Light Distribution Diagram - LED CLA 40W A60 E27 3000K CL EELA SRT AU

General uniform lighting - LED CLA 40W A60 E27 3000K CL EELA SRT AU


Classic filament LEDbulbs

Photometric data




Spectral Power Distribution Colour - LED CLA 40W A60 E27 3000K CL EELA SRT AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED CLA 40W A60 E27 3000K CL EELA SRT AU

