



Classic filament LEDbulbs

LED CLA 40W A60 E27 4000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	E27		30 mA
Nominal lifetime	50,000 h	Wattage Equivalent	40 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	50,000 h	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	Ambient temperature range	-20 to +45 °C
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	35 °C
Luminous Flux	485 lm		
Color Designation	Cool White (CW)	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	210 lm/W	Dimmable	No
Correlated Color Temperature (Nom)	4000 K		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Photobiological safety according to EN 62471	RG1	Bulb Shape	A60
Operating and Electrical		Approval and Application	
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	- kWh
Power Consumption	2.3 W	EU RoHS compliant	Yes

Classic filament LEDbulbs

EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Product Data	
Order product name	LED CLA 40W A60 E27 4000K CL EELA SRT AU
Full product name	LED CLA 40W A60 E27 4000K CL EELA SRT AU
Full product code	871951445495800



Order code	929003066519
Material Nr. (12NC)	929003066519
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.036 kg
EAN/UPC - Product/Case	8719514454958
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514454965

Dimensional drawing




Product	D	C
LED CLA 40W A60 E27 4000K CL EELA SRT AU	60 mm	105 mm

Photometric data





Spectral Power Distribution Colour - LED CLA 40W A60 E27 4000K CL EELA SRT AU

Light Distribution Diagram - LED CLA 40W A60 E27 4000K CL EELA SRT AU



Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LED CLA 40W A60 E27 4000K CL EELA SRT AU

