



Classic filament LEDbulbs

8A19/PER/UD/FR/G/E26/WGD 4/2PFT20

Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED

Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	800 lm
Color Designation	Warm Glow(WG)
Luminous Efficacy (rated) (Nom)	100 lm/W
Correlated Color Temperature (Nom)	2200 2700 K
Color Consistency	<4
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	8 W

Lamp Current (Nom)	85 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.4 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
Ambient temperature range	-4 to +104 °F

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location

Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes

Classic filament LEDbulbs

T20 compliant	Yes
LED Innovations	EyeComfort

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20
Full product name	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20


Order code	573436
Material Nr. (12NC)	929003083203
Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.073 lb
EAN/UPC - Product/Case	046677573430
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677573435

Dimensional drawing




Product	D	C
8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	2-3/8 inch	4-3/16 inch

Photometric data



Technical Parameters 13 Photometry 14 Page 107


General uniform lighting - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20



Spectral Power Distribution Colour - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20


Classic filament LEDbulbs

Photometric data




Light Distribution Diagram - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20

