



LED A15

6.6A15/PER/UD50/CL/G/E26/DIM2PF T20

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	950 [CCT of 5000K]
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	750 lm
Color Designation	Daylight
Luminous Efficacy (rated) (Nom)	113 lm/W
Correlated Color Temperature (Nom)	5000 K
Color Consistency	<4
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	6.6 W
Lamp Current (Nom)	65 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.4 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
Ambient temperature range	-4 °F to 104 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A15
UL Wet/ damp/ dry location	Wet location
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort

LED A15

Application Conditions


can it be used in closed luminaires No

Product Data

Order product name	6.6A15/PER/UD50/CL/G/E26/DIM2PF T20
Full product name	6.6A15/PER/UD50/CL/G/E26/DIM2PF T20
Order code	573402
Material Nr. (12NC)	929003084503



Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.053 lb
EAN/UPC - Product/Case	046677573409
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677573404

Dimensional drawing




Product	D	C
6.6A15/PER/UD50/CL/G/E26/DIM2PF T20	1-7/8 inch	3-5/16 inch

Photometric data



Light Distribution Diagram - 6.6A15/PER/UD50/CL/G/E26/DIM2PF T20

General uniform lighting - 6.6A15/PER/UD50/CL/G/E26/DIM2PF T20



Spectral Power Distribution Colour - 6.6A15/PER/UD50/CL/G/E26/DIM2PF T20

LED A15

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 6.6A15/PER/UD50/CL/G/E26/DIM2PF T20

