



# LED PAR38

## 13PAR38/S/120W/927 40D E27 ND/G/110-277V

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	1,200 lm
Luminous Intensity (Nom)	2,231 cd
Luminous Efficacy (rated) (Nom)	92.00 lm/W
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	13 W

Lamp Current (Max)	116 mA
Lamp Current (Min)	48 mA
Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	110-277 V

Temperature	
T-Case Maximum (Nom)	65 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	PAR38


Approval and Application	
Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
EyeComfort	Yes

# LED PAR38

LED Innovations	EyeComfort
<b>Product Data</b>	
Order product name	13PAR38/S/120W/927 40D E27 ND/G/110-277V
Full product name	13PAR38/S/120W/927 40D E27 ND/G/110-277V
Full product code	871951440693300
Order code	929003134407



Material Nr. (12NC)	929003134407
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.310 kg
EAN/UPC - Product/Case	8719514406933
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514406940

## Dimensional drawing



Product	D	C
13PAR38/S/120W/927 40D E27 ND/G/110-277V	122 mm	137 mm

## Photometric data




Light Distribution Diagram - 13PAR38/S/120W/927 40D E27 ND/G/110-277V

Accent Lighting Spots - 13PAR38/S/120W/927 40D E27 ND/G/110-277V

# LED PAR38

## Photometric data



Spectral Power Distribution Colour - 13PAR38/S/120W/927 40D E27 ND/G/  
110-277V

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 13PAR38/S/120W/927 40D E27 ND/G/  
110-277V

