



Classic filament LEDbulbs

5A19/LED/927/FR/Glass/E26/DIM 1FB T20

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED

Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	320 degree(s)
Luminous Flux	450 lm
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz

Power Consumption	5 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
Ambient temperature range	-20 °C to 45 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location

Classic filament LEDbulbs

Approval and Application

EU RoHS compliant	Yes
T20 compliant	Yes

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	5A19/LED/927/FR/Glass/E26/DIM 1FB T20
Full product name	5A19/LED/927/FR/Glass/E26/DIM 1FB T20



Order code	929003497304
Material Nr. (12NC)	929003497304
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.033 kg
EAN/UPC - Product/Case	046677578534
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677578539

Dimensional drawing



Product	D	C
5A19/LED/927/FR/Glass/E26/DIM 1FB T20	60 mm	105 mm

Photometric data




Spectral Power Distribution Colour - 5A19/LED/927/FR/Glass/E26/DIM 1FB T20

General uniform lighting - 5A19/LED/927/FR/Glass/E26/DIM 1FB T20

Classic filament LEDbulbs

Photometric data




Light Distribution Diagram - 5A19/LED/927/FR/Glass/E26/DIM 1FB T20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5A19/LED/927/FR/Glass/E26/DIM 1FB T20

