

Classic filament LEDbulbs

LED CLA 40W A60 B22 4000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

| General Information | |
|------------------------|----------------|
| Cap-Base | B22 |
| Nominal lifetime | 50,000 hour(s) |
| Switching Cycle | 50,000 |
| Rated Lifetime (Hours) | 50,000 hour(s) |
| Lighting Technology | LED |

| Light Technical | |
|--|--------------------|
| Color Code | 840 [CCT of 4000K] |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 485 lm |
| Color Designation | Cool White (CW) |
| Luminous Efficacy (rated) (Nom) | 210 lm/W |
| Correlated Color Temperature (Nom) | 4000 K |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Photobiological safety according to EN 62471 | RG1 |

| Operating and Electrical | |
|--------------------------|-------------|
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 2.3 W |

| | |
|---------------------------|-----------|
| Lamp Current (Nom) | 30 mA |
| Wattage Equivalent | 40 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.4 |
| Voltage (Nom) | 220-240 V |

| Temperature | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
| T-Case Maximum (Nom) | 35 °C |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |

| Mechanical and Housing | |
|------------------------|-------|
| Bulb Finish | Clear |
| Bulb Material | Glass |
| Bulb Shape | A60 |


| Approval and Application | |
|-------------------------------|-------|
| Energy Consumption kWh/1000 h | - kWh |
| EU RoHS compliant | Yes |

Classic filament LEDbulbs

| | |
|---------------------|--|
| EyeComfort | Yes |
| LED Innovations | UltraEfficient EyeComfort |
| Product Data | |
| Order product name | LED CLA 40W A60 B22 4000K CL EELA SRT AU |
| Full product name | LED CLA 40W A60 B22 4000K CL EELA SRT AU |
| Full product code | 871951445824600 |



| | |
|---------------------------------|---------------|
| Order code | 929003539819 |
| Material Nr. (12NC) | 929003539819 |
| Numerator - Quantity Per Pack | 1 |
| Net Weight (Piece) | 0.036 kg |
| EAN/UPC - Product/Case | 8719514458246 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8719514458253 |

Dimensional drawing



| Product | D | C |
|--|-------|--------|
| LED CLA 40W A60 B22 4000K CL EELA SRT AU | 60 mm | 105 mm |


Photometric data



© 2022 Philips Lighting B.V. Philips Lighting B.V. Page 10

Spectral Power Distribution Colour - LED CLA 40W A60 B22 4000K CL EELA SRT AU



General uniform lighting - LED CLA 40W A60 B22 4000K CL EELA SRT AU



Light Distribution Diagram - LED CLA 40W A60 B22 4000K CL EELA SRT AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LED CLA 40W A60 B22 4000K CL EELA SRT AU

