



Ecofit Ledtubes T8

Ecofit E LEDtube 1200mm 18W 740 T8 I MY

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Lamp Current (Min)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Lamp Current (Nom)	140 mA
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.5
Light Technical		Voltage (Nom)	220-240 V
Color Code	740 [CCT of 4000K]	Ballast Compatibility	EM
Beam Angle (Nom)	240 degree(s)	Temperature	
Luminous Flux	1,800 lm	Ambient temperature range	-20 °C to 45 °C
Color Designation	Cool White (CW)	T-Case Maximum (Nom)	55 °C
Luminous Efficacy (rated) (Nom)	100 lm/W	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Color Consistency	<7	Mechanical and Housing	
Color rendering index (CRI)	70	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Operating and Electrical		Product Length	1,200 mm
Line Frequency	50 to 60 Hz	Bulb Shape	T8
Input Frequency	50 to 60 Hz		
Power Consumption	18 W		
Lamp Current (Max)	140 mA		

Ecofit Ledtubes T8

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance KEMA Keur certificate
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Product Data


Order product name	Ecofit E LEDtube 1200mm 18W 740 T8 I MY
Full product name	Ecofit E LEDtube 1200mm 18W 740 T8 I MY

Full product code	871951447540300
Order code	929003550737
Material Nr. (12NC)	929003550737
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.175 kg
EAN/UPC - Product/Case	8719514475403
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514475410


Dimensional drawing

Product	D1	D2	A1	A2	A3
Ecofit E LEDtube 1200mm 18W 740 T8 I MY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Photometric data




General uniform lighting - Ecofit E LEDtube 1200mm 18W 740 T8 I MY



Spectral Power Distribution Colour - Ecofit E LEDtube 1200mm 18W 740 T8 I MY


Ecofit Ledtubes T8

Photometric data




Light Distribution Diagram - Ecofit E LEDtube 1200mm 18W 740 T8 I MY


Lifetime




Lumen Maintenance Diagram - Ecofit E LEDtube 1200mm 18W 740 T8 I MY



Life Expectancy Diagram




FailureRate



LifetimeVsTc

Ecofit Ledtubes T8

Lifetime



Lumen Maintenance Diagram - Ecofit E LEDtube 1200mm 18W 740 T8 I MY

