



Ecofit Ledtubes T8

Ecofit E LEDtube 600mm 9W 740 T8 I MY

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Lamp Current (Max)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Lamp Current (Max)	75 mA
Nominal lifetime	15,000 hour(s)	Lamp Current (Min)	75 mA
Switching Cycle	50,000	Lamp Current (Nom)	75 mA
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.5
Color Code	740 [CCT of 4000K]	Voltage (Nom)	220-240 V
Beam Angle (Nom)	240 degree(s)	Temperature	
Luminous Flux	900 lm	Ambient temperature range	-20 °C to 45 °C
Color Designation	Cool White (CW)	T-Case Maximum (Nom)	55 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	100 lm/W	Dimmable	No
Color Consistency	<7	Mechanical and Housing	
Color rendering index (CRI)	70	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Operating and Electrical		Product Length	600 mm
Line Frequency	50 to 60 Hz	Bulb Shape	T8
Input Frequency	50 to 60 Hz		
Power Consumption	9 W		

Ecofit Ledtubes T8

Approval and Application


Energy Saving Product	Yes
Approval Marks	RoHS compliance KEMA Keur certificate

Product Data

Order product name	Ecofit E LEDtube 600mm 9W 740 T8 I MY
Full product name	Ecofit E LEDtube 600mm 9W 740 T8 I MY
Full product code	871951447544100



Order code	929003550937
Material Nr. (12NC)	929003550937
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514475441
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514475458

Dimensional drawing




Product	D1	D2	A1	A2	A3
Ecofit E LEDtube 600mm 9W 740 T8 I MY	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Photometric data



General uniform lighting - Ecofit E LEDtube 600mm 9W 740 T8 I MY



Spectral Power Distribution Colour - Ecofit E LEDtube 600mm 9W 740 T8 I MY



Light Distribution Diagram - Ecofit E LEDtube 600mm 9W 740 T8 I MY



Ecofit Ledtubes T8

Lifetime




Lumen Maintenance Diagram - Ecofit E LEDtube 600mm 9W 740 T8 I MY

Life Expectancy Diagram - Ecofit E LEDtube 600mm 9W 740 T8 I MY



Life Expectancy Diagram - Ecofit E LEDtube 600mm 9W 740 T8 I MY

Life Expectancy Diagram - Ecofit E LEDtube 600mm 9W 740 T8 I MY



Lumen Maintenance Diagram

Ecofit Ledtubes T8

