



Classic filament LEDbulbs

LED CLA 7.3W A60 E27 2700K FR UE SRT6

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

| General Information | |
|---------------------|----------|
| Cap-Base | E27 |
| Nominal lifetime | 50,000 h |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |

| Light Technical | |
|--|--------------------|
| Color Code | 827 [CCT of 2700K] |
| Beam Angle (Nom) | 300 degree(s) |
| Luminous Flux | 1,535 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 210 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Photobiological safety according to EN 62471 | RG1 |

| Operating and Electrical | |
|--------------------------|-------------|
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 7.3 W |
| Lamp Current (Nom) | 71 mA |

| Wattage Equivalent | |
|---------------------------|-----------|
| Wattage Equivalent | 100 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.4 |
| Voltage (Nom) | 220-240 V |

| Temperature | |
|----------------------|-------|
| T-Case Maximum (Nom) | 70 °C |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |

| Mechanical and Housing | |
|------------------------|----------|
| Bulb Finish | Frosted |
| Bulb Material | Glass |
| Bulb Shape | A60 |
| Net Weight (Piece) | 0.039 kg |


| Approval and Application | |
|--------------------------|----------------|
| EU RoHS compliant | Yes |
| EyeComfort | Yes |
| LED Innovations | UltraEfficient |

Classic filament LEDbulbs

| | |
|---------------------------|---------------------------------------|
| Ambient temperature range | -20 to +45 °C |
| Product Data | |
| Order product name | LED CLA 7.3W A60 E27 2700K FR UE SRT6 |
| Full product name | LED CLA 7.3W A60 E27 2700K FR UE SRT6 |
| Full product code | 872016939427800 |


| | |
|---------------------------------|---------------|
| Order code | 929003625319 |
| Material Nr. (12NC) | 929003625319 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169394278 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8720169394285 |

Dimensional drawing




| Product | D | C |
|---------------------------------------|-------|--------|
| LED CLA 7.3W A60 E27 2700K FR UE SRT6 | 60 mm | 104 mm |


Photometric data



Light Distribution Diagram - LED CLA 7.3W A60 E27 2700K FR UE SRT6





Spectral Power Distribution Colour - LED CLA 7.3W A60 E27 2700K FR UE SRT6



General uniform lighting - LED CLA 7.3W A60 E27 2700K FR UE SRT6

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LED CLA 7.3W A60 E27 2700K FR UE SRT6

