



Energy Saver GU24

EL/mdTQS 18W GU24

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.


Product data

| General Information | | Lamp Current (Nom) | |
|---------------------------------------|--------------------------------|-------------------------------|---|
| Cap-Base | GU24 | | 290 mA |
| Nominal lifetime | 10,000 hour(s) | Power Factor (Fraction) | 0.55 |
| Switching Cycle | 5,000 | Voltage (Nom) | 110-127 V |
| Rated Lifetime (Hours) | 10,000 hour(s) | Controls and Dimming | |
| Lighting Technology | Compact Fluorescent Integrated | Dimmable | No |
| Light Technical | | Mechanical and Housing | |
| Color Code | 827 [CCT of 2700K] | Bulb Shape | EL/mdTQS |
| Luminous Flux | 1,250 lm | Approval and Application | |
| Color Designation | Warm White (WW) | Mercury (Hg) Content (Max) | 2 mg |
| Luminous Efficacy (rated) (Nom) | 67 lm/W | Energy Consumption kWh/1000 h | 18 kWh |
| Chromaticity Coordinate X (Nom) | 459 | Product Data | |
| Chromaticity Coordinate Y (Nom) | 412 | Order product name | 18 W (75 W) Compact fluorescent Spiral bulb |
| Correlated Color Temperature (Nom) | 2700 K | Full product name | EL/mdTQS 18W GU24 |
| Color rendering index (CRI) | 80 | Order code | 454207 |
| LLMF At End Of Nominal Lifetime (Nom) | 50 % | Material Nr. (12NC) | 929689791301 |
| Operating and Electrical | | Numerator - Quantity Per Pack | 1 |
| Line Frequency | 50 or 60 Hz | Net Weight (Piece) | 0.154 lb |
| Input Frequency | 50 or 60 Hz | EAN/UPC - Product/Case | 046677454203 |
| Power Consumption | 18.0 W | | |

Energy Saver GU24

| | |
|---------------------------------|----------------|
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 50046677454208 |

Dimensional drawing



| Product | D (max) | C (max) | F (max) |
|---|------------|------------|------------|
| 18 W (75 W) Compact fluorescent Spiral bulb | 2-1/4 inch | 4-1/8 inch | 1-7/8 inch |

