



TORNADO

24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb

The Helix range is a twist-shape compact fluorescent lamp, with optimal light distribution. It is available in 11W, 15W, 20W and 23W (25W), with lumen equivalence of 60W, 75W, 100W and 125W incandescent light bulb. It is also available in two color temperatures: warm white (2700K) and cool daylight (6500K). It is available in both 220-240V and 120-127V and able to operate under a wide voltage range (Power supply fluctuation). It consumes up to 80% less energy than the incandescent light bulb and lasts for 3 years.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information		Chromaticity Coordinate X (Nom)		313
Cap-Base	B22	Chromaticity Coordinate Y (Nom)		337
Nominal lifetime	8,000 hour(s)	Correlated Color Temperature (Nom)		6500 K
Switching Cycle	5,000	Color rendering index (CRI)		80
Rated Lifetime (Hours)	8,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)		70 %
Lighting Technology	Compact Fluorescent Integrated	Operating and Electrical		
Light Technical		Line Frequency		50 or 60 Hz
Color Code	865 [CCT of 6500K]	Input Frequency		50 or 60 Hz
Luminous Flux	1,450 lm	Power Consumption		23 W
Color Designation	Cool Daylight	Lamp Current (Nom)		170 mA
Luminous Efficacy (rated) (Nom)	63 lm/W	Starting Time (Nom)		0.3 s

TORNADO

Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Shape	Spiral
------------	--------

Approval and Application


Mercury (Hg) Content (Nom)	2 mg
Energy Consumption kWh/1000 h	23 kWh

Product Data

Order product name	24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb
--------------------	--

Full product name	24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb
Full product code	871829113817400
Order code	929689858602
Material Nr. (12NC)	929689858602
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.077 kg
EAN/UPC - Product/Case	8718291138174
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291138181

Dimensional drawing



Product	D (max)	C (max)	F (max)
24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb	61.5 mm	117 mm	50.5 mm

