

DESCRIPTION

Wall Wash Downlight with an integral specular clear kick reflector, and matte white trim ring. The trim features cast aluminum construction for high-quality fit and finish. Wall Wash Downlight uses MR16 low voltage or GU10 line voltage lamps ideal for accent and task lighting. Trim offers 360° orientation within housing.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

The 3020 Wall Wash features an integral wall wash reflector. The integral reflector design maintains a clean, uncluttered ceiling appearance while adding wall wash capability to the downlight. Halo matte white finish contributes to a clean ceiling look. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim).

3020 is designed for use with the following Halo H3 small aperture housings:

- Line Voltage Housing (for 120V GU10 lamps).

H36ICAT	50W	IC Air-Tite Housing
H36TAT	50W	Non-IC Air-Tite Housing
H36RTAT	50W	Non-IC Air-Tite Remodel Housing
- Low Voltage Housing (for 12V MR16 lamps).

H36LVICAT	50W	IC Air-Tite Housing
H36LVTAT	50W	Non-IC Air-Tite Housing
H36LVRTAT	50W	Non-IC Air-Tite Remodel Housing
H36LVTAT277	50W	Non-IC Air-Tite Housing, 120/277V
H36LVRTAT277	50W	Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps).

H38ICAT	50W	IC Air-Tite Housing
---------	-----	---------------------
- Low Voltage Housing (for 12V MR16 lamps).

H38LVICAT	37W	IC Air-Tite Housing
-----------	-----	---------------------




3020WW
Wall Wash Downlight with White Trim Ring

3020

3" Wall Wash Downlight Trim

3" TRIM



Aperture: 1-3/4" [45mm]
 Ceiling Opening: 3-3/4" [95mm]
 Outside Diameter: 4-1/4" [108mm]

ORDERING INFORMATION

SAMPLE NUMBER: 3020WW

Order housing and trims separately.

Trim	Finish
3020= 3" Wall Wash Trim	WW=White Wall Wash Trim