

PHILIPS

Virga Wall Light 4W

myGarden

2700K

Black

Water Resistant



17287/30/16



Enjoy a beautiful garden with light

Philips myGarden Virga wall light is machined from polished aluminum, its contemporary shape directing the elegant LED light away from your wall. Sure to make a strong style statement in your garden.

Sustainable light solutions

- Energy saving
- High quality LED light
- Warm white light
- Philips offers 5 year warranty on the LED module and driver

Designed for your garden

- IP44 - weather proof

Highlights

Energy saving



This Philips energy saving lamp conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Warm white light



Light can have different color temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

Specifications

Design and finishing

- Color: Black
- Material: Aluminium

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Fully weatherproof: Yes
- LED integrated: Yes

Garden area

- Garden area: Garden & Patio

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: Yes
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.400 kg
- Height: 12.2 cm
- Length: 9.2 cm
- Width: 10.3 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Light source equivalent to traditional bulb of: 30 W
- Total lumen output fixture: 400 lm
- Bulb technology: LED
- Light color: warm white
- Mains power: 50-60 Hz
- LED: Yes
- Energy class included light source: F
- Wattage bulb included: 4 W
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: No
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC - product: 8718291479581
- Net weight: 0.4 kg
- Gross weight: 0.48 kg
- Height: 13.8 cm
- Length: 10.3 cm
- Width: 12.3 cm



Issue date: 2025-02-17
Version: 0.453

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com