

PHILIPS

Spot 50W MR16
GU5.3 x4

LED

3000K

390lm

15000h

8719514327702



Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

High quality light

- Bright white light

Choose for a sustainable solution

- Safe for any room and convenient to recycle

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Type of glass: Clear
- Dimmable: No
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions

- Height: 4.6 cm
- Width: 5.1 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h
- Ambient temperature range: -20 to +40 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 60 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 390 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 830 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 390 lm
- Luminous Efficacy (rated) (Nom): 78 lm/W

Other characteristics

- Efficacy: 78 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514327702
- EOC: 871951432770200
- Product title: LEDspots 5-50W MR16 830 60D 4PK

Power

- Power Factor (Fraction): 0.6

Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Power Consumption: 5 W

Product dimensions and weight

- Length: 4.6 cm

Rated values

- Rated lifetime: 15,000 h
- Rated peak intensity: 400 cd

Technical specifications

- Frequency: - Hz
- Line Frequency: - Hz
- Dimmable: No
- Cap-Base: GU5.3

Packaging dimensions & weight

- EAN/UPC - product: 8719514327702
- Net weight: 0.16 kg
- Gross weight: 0.2 kg
- Height: 12.4 cm
- Length: 5.1 cm
- Width: 10.5 cm



Issue date: 2025-02-02
Version: 0.97

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com