

# PHILIPS

Bulb 60W A60 E27

LED

2700K

806lm

15000h

Dimming

8719514333598



## Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### Light beyond illumination

- Dimmable

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: Yes

## Bulb dimensions

- Height: 11 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: instant full light
- Color Code: 927 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 94 lm/W

## Packaging information

- EAN: 8719514333598
- EOC: 871951433359800
- Product title: LEDBulb 8.5-60W A60 E27 2700K FR D AU/NZ

## Power consumption

- Power factor: 0.9
- Voltage: 220-240 V
- Wattage: 8.5 W
- Wattage equivalent: 60 W

## Product dimensions and weight

- Length: 11 cm

8719514333598

#### Technical specifications

- Frequency: 50-60 Hz

#### Packaging dimensions & weight

- EAN/UPC - product: 8719514333598
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm
- Material number (12NC):  
929002069119



Issue date: 2024-07-07  
Version: 0.320

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)