

PHILIPS

Filament Candle
Frosted 40W P45 B22

LED

2700K

470lm

15000h

8719514388291



Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

High quality light

- Designed for the comfort of your eyes

Create the right light for your home

- Perfect for general room lighting

Light beyond illumination

- Vintage style, modern LED technology

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Vintage style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: B22
- Type of glass: Frosted
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Glass

Bulb dimensions

- Height: 7.6 cm
- Width: 4.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000 h
- Ambient temperature range: -20 to +45 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 827 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 470 lm
- Luminous Efficacy (rated) (Nom): 134 lm/W

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 134 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514388291
- EOC: 871951438829100
- Product title: LEDclassic 40W P45
2700K B22 ND FR AU

Power

- Power Factor (Fraction): 0.41

Power consumption

- Power factor: 0.41
- Voltage: 220–240 V
- Wattage: 3.5 W
- Wattage equivalent: 40 W
- Power Consumption: 3.5 W

Product dimensions and weight

- Length: 7.6 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50–60 Hz
- Dimmable: No
- Cap-Base: B22

Packaging dimensions & weight

- EAN/UPC - product: 8719514388291
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 10.1 cm
- Length: 5.5 cm
- Width: 5.5 cm
- Material number (12NC):
929002379079



Issue date: 2024-11-18
Version: 0.54

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com