

# PHILIPS

Filament Bulb Frosted  
100W A60 B22

UltraEfficient

4000K

1535lm

50000h

8720169394339



## UltraEfficient lamp, our most energy efficient LED bulbs

Philips UltraEfficient LED lamps provide beautiful light, offer an exceptionally long lifetime of 50,000 hours, and deliver immediate and significant energy savings. Reduce the frequency of lamp replacements and enjoy light that's easy on the eyes with our trusted EyeComfort design.

### **Choose for a sustainable solution**

- Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 40% in energy compared to standard Philips LED bulbs.

### **Designed to last longer and save more energy**

- Long life bulb - Lasts up to 50 years

# Highlights

**Saves over 40% energy compared to standard LED**

**Long life bulb - Lasts up to 50 years**

Avoid the hassle of frequent light bulb replacements. With a lifetime of up to

50,000 hours, our UltraEfficient LEDs last 3.5 times longer than standard Philips LEDs, so you can enjoy a perfect lighting solution for more than 50 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Glass

## Bulb dimensions

- Height: 10.2 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 1535 lm

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort, UltraEfficient

## Other characteristics

- Efficacy: 210 lm/W

## Packaging information

- EAN: 8720169394339
- EOC: 872016939433900
- Product title: LED CLA 7.3W A60 B22 4000K FR UE SRT6

## Power consumption

- Power factor: 0.4
- Voltage: AC 220-240 V
- Wattage: 7.3 W
- Wattage equivalent: 100 W

## Product dimensions and weight

- Length: 10.2 cm

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions & weight

- EAN/UPC - product: 8720169394339
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 12.2 cm
- Length: 6.4 cm
- Width: 6.6 cm



Issue date: 2024-12-04  
Version: 0.68

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)