

LED STANDARDS DEPOLIES

LAMPES



15 000 h



Non gradable



2ans
Garantie



E27

Désignation	Flux	Conso.	Efficacité Lumineuse	Température de couleur	Dimensions	Classe énerg.	Code
	lm	W	[Lm/W]	K	mm		
MZD LED 40W A60 E27 827 FR ND	470	4.9	95	2700	60 x 107		54051100
MZD LED 40W A60 E27 840 FR ND	470	4.9	95	4000	60 x 108		54053500
MZD LED 60W A60 E27 827 FR ND	806	8	100	2700	60 x 108		54057300
MZD LED 60W A60 E27 840 FR ND	806	8	100	4000	60 x 108		54059700
MZD LED 60W A60 B22 827 FR ND	806	8	100	2700	60 x 105		54065800
MZD LED 60W A60 E27 827 FR ND (Lot de 10)	806	8	100	2700	60 x 108		54129700
MZD LED 75W A60 E27 827 FR ND G3	1055	10	105	2700	60 x 108		54093100
MZD LED 75W A60 E27 840 FR ND G3	1055	10	105	4000	60 x 108		54095500
MZD LED 75W A60 E27 CDL FR ND G3	1055	10	105	6500	60 x 108		54091700
MZD LED 100W A60 E27 WW FR ND	1521	13	117	2700	60 x 120		54045000
MZD LED 100W A60 E27 CW FR ND G3	1521	13	117	4000	60 x 120		54063400
MZD LED 100W A60 E27 CDL FR ND G3	1521	13	117	6500	60 x 120		54047400