

HID Replacement LED lamp product matrix

Find the right lamp for every application

Get the perfect-fit with our new line of smaller, lighter HID replacement lamps – because size matters!

Applications																												
MH Wattage	<ul style="list-style-type: none"> High ceilings Schools Gymnasium Warehouses Retail 			<ul style="list-style-type: none"> Street lighting Pedestrian Walkways 			<ul style="list-style-type: none"> Street lighting Walkways 			<ul style="list-style-type: none"> Parking lots Public spaces 			<ul style="list-style-type: none"> Street lighting Roadway lighting 			<ul style="list-style-type: none"> Outdoor walls of commercial structures 			<ul style="list-style-type: none"> Indoor warehouses Parking garages 			<ul style="list-style-type: none"> Visual & Security Outdoor commercial structures 						
	HigW HBay/LowBay			Post Top			Tear Drop			ShoeBox/Area			Cobra head			Wall pack			Canopy/Ceiling			Flood/Landscape						
< 50	 18W CC	 15W glass	 25W glass	 18W CC	 15W glass	 25W glass	 18W CC	 15W glass	 25W glass	 18W CC	 15W glass	 25W glass	 20WP/850	 18W CC	 15W glass	 25W glass	 20WP/850	 18W CC	 15W glass	 25W glass	 20WP/850	 18W CC	 15W glass	 25W glass	 18W CC	 15W glass	 25W glass	
70	 27W CC	 25W glass	 34W glass	 27W CC	 25W glass	 34W glass	 27W CC	 25W glass	 34W glass	 27W CC	 25W glass	 34W glass	 20WP/850	 27W CC	 25W glass	 34W glass	 20WP/850	 27W CC	 25W glass	 34W glass	 20WP/850	 27W CC	 25W glass	 34W glass	 27W CC	 25W glass	 34W glass	
100	 36W CC	 45W CC	 34W glass	 45W glass	 36W CC	 45W CC	 34W glass	 45W glass	 36W CC	 45W CC	 34W glass	 45W glass	 40WP	 36W CC	 45W CC	 34W glass	 45W glass	 40WP	 36W CC	 45W CC	 34W glass	 45W glass	 40WP	 36W CC	 45W CC	 34W glass	 45W glass	
150	 63W CC	 80W CC	 54W glass	 63W CC	 80W CC	 54W glass	 63W CC	 80W CC	 54W glass	 63W CC	 80W CC	 54W glass	 60WP	 63W CC	 80W CC	 54W glass	 60WP	 63W CC	 80W CC	 54W glass	 60WP	 63W CC	 80W CC	 54W glass	 63W CC	 80W CC	 54W glass	
175	 54W CC	 63W CC	 45W glass	 54W glass	 54W CC	 63W CC	 45W glass	 54W glass	 54W CC	 63W CC	 45W glass	 54W glass	 60WP	 54W CC	 63W CC	 45W glass	 54W glass	 60WP	 54W CC	 63W CC	 45W glass	 54W glass	 60WP	 54W CC	 63W CC	 45W glass	 54W glass	
250	 80W CC	 115W CC	 145W HB		 80W CC	 115W CC	 145W HB		 80W CC	 115W CC	 145W HB		 80W CC	 115W CC	 145W HB		 80W CC	 115W CC	 145W HB		 80W CC	 115W CC	 145W HB		 80W CC	 115W CC	 145W HB	
400	 145W CC	 150W CC	 145/165 HB		 145W CC	 150W CC	 145/165 HB		 145W CC	 150W CC	 145/165 HB		 145W CC	 150W CC	 145/165 HB		 145W CC	 150W CC	 145/165 HB		 145W CC	 150W CC	 145/165 HB		 145W CC	 150W CC	 145/165 HB	
1000	 450W CC			 450W CC			 450W CC			 450W CC			 450W CC			 450W CC			 450W CC			 450W CC						

■ CCT/Color selectable lamp option is also available. ■ Wall pack lamp.