

**PHILIPS**


Home Decorative



# Philips Decorative Lighting Collection








You've built a home, and lovingly furnished it to make it your own. A lush sofa set to lounge in comfort, an elegant dining table for family meals and sleek cupboards to hold your possessions. However, no home is complete until the lights are turned on to bathe everything in a welcoming glow.

Philips has lights for every style. For the proud homeowner, Philips offers the Home Lighting Decorative Collection consisting of Modern Living, Contemporary, Chic, Vibrant Expressions, Heritage Refined and Timeless Classics, stylistic genres that span the home decor spectrum that's just right for your home.

Light up your lifestyle today.







Chandeliers	6
Lead Families	36
Pendant & Ceiling	60
Wall Lights	82
Downlighters	108
Decorative Fans	128
Cove Lights	130
Spot Lights	134
Bathroom	142
Track Light	154
Outdoor	158







# CHANDELIERS

Chandeliers stand for grandeur of your home. The perfect multilayer crystal chandelier can setup the design context of your entire home.

A crystal chandelier is great amalgam of material and design. The design sensibility of Philips and material assurance of genuine crystal in each of the products ensures that the products stays new and retains its shine for many years and so does your house.

With Le Cristal, Philips takes lighting into a different league. A league where art, design and technology come together to create an experience that lives up to the tastes of people.

Philips has a nice assortment of crystal chandeliers to match your taste and sensibilities.

The refined art of elegance, now in a new light.





# Caesar

Model No.: 581864

Finest crystals in contemporary stainless steel finish for a royal look.



Model No.: 581863

Exclusive crystals in refined stainless steel finish to add glamour to your home.

Model No.: 581865

Premium crystals in aesthetic stainless steel finish for the ultra-modern house.



	Chandelier	Chandelier	Wall Light
Model No.	581863	581864	581865
Colour	Mirror stainless steel	Mirror stainless steel	Mirror stainless steel
Material	Beaded with class A clear crystal	Beaded with class A clear crystal	Beaded with class A clear crystal
Dimensions (mm)	400x400x190	Dia. 465 x H 1450	Dia 13 x W 130 x H 210
Lamp Base	G9	G9	G9
Wattage	5x42W Max*	6x42W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V/50 Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used





# Corona

Model No.: 581846

Finest crystals in superb chrome finish to add style to your house.



Model No.: 581847

Superior-grade crystals set in mirror stainless steel with chrome finish for refined decor.

Model No.: 581886

Choicest crystals with chrome finish in a contemporary design for a modern feel.



	Chandelier	Chandelier	Chandelier
Model No.	581846	581847	581886
Colour	Chrome	Chrome	Chrome
Material	Mirror stainless steel shade with clear crystal		Stainless steel
Dimensions (mm)	Dia. 510 x H 1440	Dia. 510 x H 180	680x220x750
Lamp Base	G9	G9	G9
Wattage	7x42W Max*	7x42W Max*	5x33W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V/50 Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used





# Monarch

Model No.: 581857

Choicest crystals with chrome finish in a grand heritage design for a royal feel.



Model No.: 581858

Impressive crystals with chrome finish in a bespoke heritage design.



Model No.: 581885

Choicest crystals with chrome finish in a grand heritage design for a royal feel.

	Chandelier	Wall Light	Chandelier
Model No.	581857	581858	581885
Colour	Chrome	Chrome	Chrome
Material	Woven laser cut anodized silver aluminium rod diffuser with clear crystal		
Dimensions (mm)	Dia. 660 x H 1800	Dia 180 x H 240	Dia. 770 x H 2400
Lamp Base	E14	E14	E14
Wattage	6x60W Max*	1x60W Max*	9x60W Max*
Lumen/CCT	Non-Integrated LED luminaire		



Model No.: 581843



# Allure

Model No.: 581842

Exclusive crystal pendant light in chrome finish for homes with a personality.



Model No.: 581843

Unique crystal pendant in a special French gold finish to add a touch of sparkle to your special house.

	Chandelier	Chandelier
Model No.	581842	581843
Colour	Chrome	French gold
Material	Class A clear crystal	Class A clear crystal
Dimensions (mm)	Dia 400 x H 1680	Dia. 300 x H 360
Lamp Base	G9	G9
Wattage	5x42W Max*	4x42W Max*
Lumen/CCT	Lumen/CCT-Non-Integrated LED luminaire	

Voltage: 240V/50 Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used





# Corral & Chalice



Model No.: 581845

Extraordinary crystals in an elegant stainless steel finish for that wondrous light spread.



Model No.: 581841

Sophisticated chandelier made of the choicest glass crystals in chrome finish to compliment your luxurious home.



Model No.: 581906

	Chandelier	Chandelier	Chandelier
Model No.	581845	581841	581906
Colour	Mirror stainless steel	Mirror stainless steel	Chrome
Material	Woven laser cut anodized silver aluminium rod diffuser with clear crystal	Class A clear crystal & cognac glass	Class A clear crystal & cognac glass
Dimensions (mm)	510x510x185	Dia. 520 x H 220	Dia 650 x H 250
Lamp Base	G9	G9	G9
Wattage	5x33W Max*	6x42W Max*	8x33W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 220V/50Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used





# Crescent

Model No.: 581844

Sumptuous ivory gold finish crystal pendant to give an exclusive feeling to your house.



Model No.: 581884

Sumptuous crystal pendant in chrome finish gives an exclusive feeling to your house.

	Chandelier	Chandelier
Model No.	581844	581884
Colour	Ivory gold metal frame clear crystal	Chrome
Material	Metal	Metal
Dimensions (mm)	Dia. 460 x H 1840	Dia. 480 x H 650
Lamp Base	G9	G9
Wattage	5x42W Max*	5x42W Max*
Lumen/CCT	Non-Integrated LED luminaire	



Model No.: 581849



# Cameo

Model No.: 581849

Unequaled crystals set in stainless steel finish chandelier for your plush interiors.



Model No.: 581850

Designer stainless steel finish chandelier with premium crystals for your lavish home.

	Chandelier	Chandelier
Model No.	581849	581850
Colour	Mirror stainless steel	Mirror stainless steel
Material	Mirror stainless steel & clear crystal	Mirror stainless steel & clear crystal
Dimensions (mm)	Dia. 580 x H 250	L 410 x W 410 x H 220
Lamp Base	G9	G9
Wattage	5x33W Max*	5x33W Max*
Lumen/CCT	Non-Integrated LED luminaire	





# Splendora

Model No.: 581903

Finest crystals in superb chrome finish to add style to your house.



Model No.: 581904

Superior-grade crystals set in mirror stainless steel with chrome finish for refined decor.



Model No.: 581905

Choicest crystals with chrome finish in a grand heritage design for a royal feel.

	Chandelier	Chandelier	Single Head Wall Light
Model No.	581903	581904	581905
Colour	Chrome	Chrome	Chrome
Material	Metal	Metal	Metal
Dimensions (mm)	Dia. 575 x H 1743	Dia. 575 x H 213	W 190 x H 175 x D 112
Lamp Base	G9	G9	G9
Wattage	7x42W Max*	7x42W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V/50 Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581901



# Torrent

Model No.: 581901

Finest crystals in contemporary stainless steel finish for a royal look.



Model No.: 581902

Premium crystals in aesthetic stainless steel finish for the ultra-modern house.

	Chandelier	Wall Lamp
Model No.	581901	581902
Colour	Chrome	Chrome
Material	Stainless steel with clear crystal	
Dimensions (mm)	Dia. 550 X H 570	W 160 X H 240 X D 80
Lamp Base	G9	G9
Wattage	8x33W Max*	2x33W Max*
Lumen/CCT	Non-Integrated LED luminaire	





# Mushroom

Model No.: 581861

An aspirational look with clear curving glass molded in mushroom strip with an elegant chrome finish.



Model No.: 581862


Clear curving glass molded in mushroom strip with chrome finish for your contemporary home.

	Chandelier	Chandelier
Model No.	581861	581862
Colour	Chrome	Chrome
Material	Clear curving glass mushroom strip	Clear curving glass mushroom strip
Dimensions (mm)	Dia. 590 x H 280	Dia. 590 x H 1440
Lamp Base	G9	G9
Wattage	6x42W Max*	6x42W Max*
Lumen/CCT	Non-Integrated LED luminaire	Non-Integrated LED luminaire

Voltage: 240V/50 Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581853





# Regalia

Model No.: 581853

Contemporary design made of superior pressed clear glass in chrome finish to brighten up your home.



Model No.: 581852

Classic wall light made of pressed clear glass with chrome finish for elite homes.



Model No.: 581851

Wall light made of premium glass to add an exquisite sparkle to your lovely home.



	Chandelier	Double Head Wall Light	Single Head Wall Light
Model No.	581853	581852	581851
Colour	Chrome	Chrome	Chrome
Material	Machine pressed clear glass & metal		
Dimensions (mm)	Dia. 760 x H 1460	100x230x150	90x80x150
Lamp Base	G9	G9	G9
Wattage	12x42W Max*	2x42W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V/50 Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581859



# Blossom



Model No.: 581859

Unparalleled amber glass design in chrome finish for a stylish home.



Model No.: 581860

	Chandelier	Chandelier
Model No.	581860	581859
Colour	Chrome & Amber	Chrome & Amber
Material	Pressed amber glass	Pressed amber glass
Dimensions (mm)	Dia. 549 x H 294	Dia. 500 x H 1740
Lamp Base	E27	E27
Wattage	4x40W Max*	4x40W Max*
Lumen/CCT	Non-Integrated LED luminaire	

Voltage: 240V/50 Hz. | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used





# Adonis

Model No.: 581855

Premium vacuum glass for sparkling light effect in elegant red copper finish, curated for designer homes.



Model No.: 581856

Aesthetic design in premium vacuum glass in red copper and chrome finish for that timeless feel.

	Chandelier	Chandelier
Model No.	581855	581856
Colour	Red copper	Chrome & Red copper
Material	Vacuum plated glass in half red copper and half clear	Vacuum plated glass in red copper
Dimensions (mm)	Dia. 770 x H 1780	Dia. 770 x H 1780
Lamp Base	G9	G9
Wattage	10x28W Max*	10x28W Max*
Lumen/CCT	Non-Integrated LED luminaire	Non-Integrated LED luminaire

Voltage: 240V / 50 Hz | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used





# Umbra



Model No.: 581854

Distinctive chandelier in nest glass with chrome & red copper finish for that unique style.

	Chandelier
Model No.	581854
Colour	Chrome & red copper
Material	Borosilicate double capsule glass inside, clear glass outside
Dimensions (mm)	Dia. 720 x H 960
Lamp Base	G9
Wattage	8x33W Max*
Lumen/CCT	Non-Integrated LED luminaire.

Voltage: 240V / 50 Hz | \*Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used







# LEAD FAMILIES

The fixtures in your homes set the overall tone for the entire décor of the house. Line coordinated fixtures bring consistency in the overall home décor. They bring predictability and subtlety to the entire home.

Philips has extensive range of coordinated designs to adorn your home. The coordinated ranges reflect all design aesthetics and present all fixtures and forms.

So, go ahead and pamper your home with our carefully assorted line just for the discerning you!





# Outline



Model No. 40937



Model No. 40938



Model No. 40936



Model No. 40939

## Luxury for your home

For those who value their family, heritage and culture and appreciate craftsmanship and lifestyle of the bygone era.

Outline range brings back the warm memories of the past; traditions and cultures through designs inspired by craftsmanship, materials and symbolic shapes, so that you can relive the past and yet enjoy the benefits and convenience of modern times.

- Classical design with antique bronze finish
- Natural diffused light
- 3 level brightness control through wall switch

	Wall Light	Table Light	Suspension Light	Floor Lamp
Model No.	40937	40938	40936	40939
Colour	Bronze	Bronze	Bronze	Bronze
Material	Metal, Glass	Metal, Glass	Metal, Glass	Metal, Glass
Dimensions(mm)	186x350x218	298x186x450	648x648x800	280x462x1500
Lamp Base	1 LED Integrated	1 LED Integrated	5 LED Integrated	1 LED Integrated
Wattage	9W	9W	37W	14W
Lumen/CCT	330lm	330lm	1900lm	540lm

Voltage: 220-240V





# Jazz



Model No. 58145



Model No. 58145



Model No. 58150



Model No. 58147



Model No. 58148



Model No. 58149

## The heart of your décor

The collection is inspired from the rhythm developed from ragtime and blues and characterized by propulsive syncopated rhythms varying degrees of improvisation. It has rhythm, which will be the heartbeat of the home. These lights are commanding yet sophisticated with its curved stems and shades.

- Beautiful light pattern
- Classic Indian appeal
- Matt gold for superior finish

	Wall Light Single	Wall Light Double	Pendant Single	3 Head Pendant	Table Lamp	Floor Lamp
Model No.	58145	58145	58147	58148	58149	58150
Colour	Matt Gold and Black		Matt Gold	Matt Gold	Matt Gold and Black	
Material	Aluminium & Metal		Aluminium & Metal		Aluminium & Metal	
Dimensions (mm)	256x118x190	256x118x190	225x225x1570	225x225x1675	220x220x620	300x300x1650
Lamp Base	E27	E27	E27	E27	E27	E27
Wattage	1x20W Max	2x20W Max	1x20W Max	3x20W Max	1x20W Max	1x20W Max
Lumen/CCT	–	–	–	–	–	–

Voltage: 220-240V | Recommended to be used with Hue WA and WACA bulb, lamp excluded



Model No. 58137



Model No. 58140



Model No. 58148



# Roseate



Model No. 58135



Model No. 58135



Model No. 58140



Model No. 58137



Model No. 58139



Model No. 58138

## A ray of class

The association of roses is with optimism, and 'Roseate' is no exception. Enjoy the look of this range with elegant hanging, wall, floor & table options. This will be perfect for home designed to inspire class. The design is not only unique but also in-vogue and elegant.

- Beautiful light pattern
- Classic Indian appeal
- Matt gold for superior finish

	Wall Light Single	Wall Light Double	Pendant Single	3 Head Pendant	Table Lamp	Floor Lamp
Model No.	58135	58135	58137	58138	58139	58140
Colour	Matt Gold	Matt Gold	Matt Gold	Matt Gold	Matt Gold	Matt Gold
Material	Aluminium & Metal		Aluminium & Metal		Aluminium & Metal	
Dimensions (mm)	135x175x290	370x175x290	325x325x1675	325x325x1675	220x220x450	325x325x1450
Lamp Base	E27	E27	E27	E27	E27	E27
Wattage	2x20W Max*	2x20W Max*	1x20W Max*	3x20W Max*	1x20W Max*	1x20W Max*
Lumen/CCT	-	-	-	-	-	-

Voltage: 220-240V | Recommended to be used with Hue WA and WACA bulb | \*Lamp excluded



Model No. 31433



Model No. 31426



Model No. 31434



# Muziris



Model No. 31433



Model No. 31427



Model No. 31428



Model No. 31434



Model No. 31425



Model No. 31426

## Delightful by design

The aesthetic design with superior finish will elevate the look of your living space. The minimal clean cut design ensures easy maintenance and cleaning of the fixtures.

- Expressive and elegant form
- Perfect for energy saving lamps
- Premium finish for superior feel

	Wood Pendant	Conical Fabric Pendant	Cylindrical Fabric Pendant	Single Head Wall Light	Double Head Wall Light	Laminar Wall Light
Model No.	31433	31427	31428	31425	31426	31434
Colour	Bronze	Bronze	Bronze	Bronze	Bronze	Bronze
Material	Aluminium & Wood	Metal	Metal	Metal	Metal	Metal
Dimensions (mm)	310x310x270	305x305x395	224x224x270	150x115x227	150x272x227	200x140x380
Lamp Base	E27	E27	E27	E27	E27	E27
Wattage	1x20W Max	1x20W Max	1x20W Max	1x20W Max	2x20W Max	1x20W Max
Lumen/CCT	-	-	-	-	-	-

Voltage: 220-240V | Recommended to be used with Hue WA and WACA bulb





# Muziris



Model No. 31431



Model No. 31432



Model No. 31429



Model No. 31430

## A new form of luxury

- Expressive and elegant form
- Matt black and rose gold for superior feel
- Perfect for energy saving lamps
- Glass shade

	1 Head Cylindrical Pendant	3 Head Cylindrical Pendant	1 Head Gold Cylindrical Pendant	3 Head Gold Cylindrical Pendant
Model No.	31429	31430	31431	31432
Colour	Black & White	Black & White	Rose Gold	Rose Gold
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	122x122x300	275x275x300	122x122x300	275x275x300
Lamp Base	E27	E27	E27	E27
Wattage	1x20W Max	3x20W Max	1x20W Max	3x20W Max
Lumen/CCT	-	-	-	-

Voltage: 220-240V | Recommended to be used with Hue WA and WACA bulb



# Muziris



Model No. 31402



Model No. 31403

## Express mood elegantly

- Flexible neck for adjusting beam
- Bronze finish for superior feel
- Long life LED light source

	Picture Light	Picture Light
Model No.	31402	31403
Colour	Bronze	Bronze
Material	Aluminium	Aluminium
Dimensions (mm)	355x180x95	500x80x95
Lamp Base	LED	LED
Wattage	7W	12W
Lumen/CCT	270lm/3000K	420lm/3000K





# Grandeur



Model No. 58071



Model No. 58071



Model No. 58072

## The warm glow of richness

The word Grandeur describes things that are distinguished, extraordinary & impressive in scope. This range has classic design with hammered glass paired with the warm glow of light to bring richness in the room.

- Expressive and elegant form
- Beautiful light pattern
- Bronze finish for superior feel
- Classic Indian appeal

	Wall Light Single	Wall Light Double	3 Head Pendant
Model No.	58071	58071	58072
Colour	Brush bronze metal base with hammered glass		
Material	Metal	Metal	Metal
Dimensions (mm)	125x125x260	280x160x260	260x260x1500
Lamp Base	E27	E27	E27
Wattage	1x20W Max*	2x20W Max*	3x20W Max*
Lumen/CCT	-	-	-

Voltage: 240V / 50Hz | Recommended to be used with Hue WA and WACA bulb | \*Bulb excluded



Model No. 581871



Model No. 581873



Model No. 581872



# Floret



Model No. 581871



Model No. 581872



Model No. 581873

## Let beauty light up your lifestyle

Flowers are a gift to this earth. Enjoy the beautiful floret range to redefine your style statement .

- Modern design for elegant look.
- Long life LED light source.
- Robust metal construction.
- Superior glass quality

	Table Lamp	Single Wall Lamp	Double Wall Lamp
Model No.	581873	581871	581872
Colour	Chrome		
Material	Metal with premium glass		
Dimensions (mm)	170x120x400	115x115x150	260x115x150
Lamp Base	LED	LED	LED
Wattage	6W*	6W*	12W*
Lumen/CCT	350lm/3000K	350lm/3000K	700lm/3000K



Model No. 581876



Model No. 581877



Model No. 581878

# Striker



Model No. 581876



Model No. 581877



Model No. 581878

## The art of simplicity

You don't always have to make grand entrance to stand out, sometimes simple yet elegant choices makes the difference. Enjoy the classic Striker range to highlight your living space.

- Beautiful light pattern
- Premium fabric material
- Superior finish

	Wall Lamp	Table Lamp	Floor Lamp
Model No.	581876	581877	581878
Colour	Chrome with fabric white shade		
Material	Metal		
Dimensions (mm)	250x220x225	220x220x420	350x350x1620
Lamp Base	E27	E27	E27
Wattage	1x40W Max*	1x40W Max*	1x40W Max*
Lumen/CCT	–	–	–

Voltage: 240V / 50Hz | Recommended to be used with Hue WA and WACA bulb | \*Lamp not included





# Sierra & Arc



Model No. 581874



Model No. 581874



Model No. 581875

## The magic of minimalism

Enjoy the look of this minimalist floor lamp range designed to inspire class. The design is not only unique but also in-vogue and elegant.

- Minimalist design, looks great with any décor
- Adds elegance to your home or office
- Metal body, fabric shade

	Floor Lamp	Floor Lamp	Floor Lamp
Model No.	581874	581874	581875
Colour	Black	White	White
Material	Metal	Metal	Metal
Dimensions (mm)	340x340x1550	340x340x1550	1180x340x1800
Lamp Base	E27	E27	E27
Wattage	1x40W Max*	1x40W Max*	1x40W Max*
Lumen/CCT	–	–	–

\* Included. Voltage: 220-240V









Model No. 37934



Model No. 37932

## Express your style with light

Give your abode that regal look with this collection of floral semi-flushed ceiling and wall lights. Forged in the classical style from premium blown glass and steel, this collection is available in 5 head ceiling light in bronze.

- Designed coordinated family
- Premium heritage bronzed finish
- Adjustable height

	Chandelier	Wall Light
Model No.	37932	37934
Colour	Bronze	Bronze
Material	Floral blown glass, Metal	Floral blown glass, Metal
Dimensions (mm)	160x230x200	520x520x850
Lamp Base	E27	E27
Wattage	5x12W Max	1x12W Max
Lumen/CCT	270lm/3000K	420lm/3000K



# PENDANT & CEILING



Pendants are the in-thing. They occupy little space and are extremely practical fixtures. These versatile fixtures are a great tool to provide either task, ambient, accent or decorative lighting.

Merge the tasks with right design and finish and the overall décor of the house gets elevated manifold.

Philips has an extensive collection of pendants for all kinds of moods and requirements. The finishes range from heritage to modern. There are some ranges which are timeless, they justify being placed in any corner of the house and accentuate it for many years!





# Ceiling & Suspension Light



Model No. 30899



Model No. 30899

## Sheer elegance

This collection is created to relive old world, luxurious environment, yet has refinement and relevance to the modern times. These luminaires create an atmosphere of elegance, formality and detail. Fit for a regal home that speaks of status, designed tastefully to experience luxury.


- Premium glass crystals for sparkling light effect
- Comforting night light

	Ceiling Light	Suspension Light
Model No.	30898	30899
Colour	Metallic black	Metallic black
Material	Glass, Crystal	Glass, Crystal
Dimensions (mm)	400x400x220	400x400x1750
Lamp Base	E27	E27
Wattage	42W*	42W*
Lumen/CCT	-	-

Voltage: 220-240V | \*Bulb excluded



Model No. 40913



Model No. 40917



# Smart Volume Ring, Sandalwood Pendant



Model No. 40913



Model No. 40917

## The art of light and shadow

The Philips Smart Volume pendants incorporate geometric shapes, reminiscent of 1950's Italian design. The result is striking pendants which combine light and shadow to create art around the room when illuminated.

- Contemporary design
- High quality durable material

	Pendant	Pendant
Model No.	40913	40917
Colour	White	White
Material	Synthetic	Synthetic
Dimensions (mm)	503 X 503 X 580	281 X 111 X 280
Lamp Base	E27	E27
Wattage	1 x 20W Max	1 x 20W Max
Lumen/CCT	-	-

Voltage: 230 | \*Bulb excluded. Recommended to be used with Hue WA and WACA Bulb



# Ecru, Apollo



Model No. 40950



Model No. 41231

## Transform the atmosphere

The design of this lamp creates a wonderful lighting effect to enhance the atmosphere in your living space. It transforms the fascinating combination of light and shadow of the room when turned on.

- Contemporary design
- High quality durable material

	Pendant	Pendant
Model No.	40950	41231
Colour	White	White
Material	Synthetic	Metal
Dimensions (mm)	572x455x1855	40x400x1500
Lamp Base	E27	E27
Wattage	1x20W Max*	1x20W Max*
Lumen/CCT	-	-

Voltage: 220V-240V / 50-60 Hz | \*Bulb excluded. Recommended to be used with Hue WA and WACA Bulb





# Panache



Model No. 58130



Model No. 58130



Model No. 58130

## Turn on elegance

If you do something with panache, you do it in a confident, stylish, and elegant way. This range of lamp creates a wonderful lighting effect to enhance the atmosphere in your living space. It transforms the fascinating combination of light and shadow of the room when turned on.

- High quality material
- Adjustable suspension height

	Pendant	Pendant	Pendant
Model No.	58130	58130	58130
Colour	Silver and Blue	Stainless Steel & White	Turtle Green & White
Material	Aluminium	Stainless Steel	Aluminium
Dimensions (mm)	410x410x1500	410x410x1500	410x410x1500
Lamp Base	E27	E27	E27
Wattage	1x20W Max*	1x20W Max*	1x20W Max*
Lumen/CCT	-	-	-

Voltage: 220V-240V / 50-60 Hz | \*Bulb excluded. Recommended to be used with Hue WA and WACA bulb





# Beacon & Gleam



Model No. 58074



Model No. 58074



Model No. 58125



Model No. 58125

## Let happiness glow

The shine that expresses an emotion of happiness. Made from high quality metal, it diffuses light to a warm even glow. It lights up to delight and soothe.

- High quality material
- Adjustable suspension height

	Pendant	Pendant	Pendant	Pendant
Model No.	58074	58074	58125	58125
Colour	Wine & Silver	Rosegold & Silver	Copper	Chrome
Material	Aluminium	Aluminium	Stainless Steel	Stainless Steel
Dimensions (mm)	157x157x1500	157x157x1500	215x215x1500	215x215x1500
Lamp Base	E27	E27	E27	E27
Wattage	1x20W Max*	1x20W Max*	1x20W Max*	1x20W Max*
Lumen/CCT	-	-	-	-

Voltage: 220V/50Hz | \*Bulb excluded. Recommended to be used with Hue WA and WACA Bulb



# Blithe



Model No. 58708



Model No. 58708



Model No. 58706



Model No. 58706

## Patterns of beauty

The shine that expresses an emotion of happiness. Made from high quality metal, it diffuses light to a warm even glow. It lights up to delight and soothe.

- Expressive & elegant form
- Beautiful light patterns

	Three Head Pendant	Three Head Pendant	Three Head Pendant	Three Head Pendant
Model No.	58076	58076	58078	58078
Colour	Wine & Silver	Rosegold & Silver	Wine & Silver	Rosegold & Silver
Material	Metal base / Aluminium shade			
Dimensions (mm)	350x350x1500	350x350x1500	550x350x1500	550x350x1500
Lamp Base	E27	E27	E27	E27
Wattage	3x20W Max*	3x20W Max*	3x20W Max*	3x20W Max*
Lumen/CCT	-	-	-	-

Voltage: 220V/50Hz | \*Bulb excluded. Recommended to be used with Hue WA and WACA bulb





# Tawny



Model No. 58127

## Go iconic, be timeless

Enjoy iconic design with a vintage lamp that perfectly fits your personal style. The Philips Tawny pendant is made of hammered glass with shiny copper base. The timeless design looks great in both modern & retro interiors.

- High quality material
- Beautiful light pattern with premium hammered luster glass
- Adjustable suspension height

	Pendant
Model No.	58127
Colour	Shiny Copper
Material	Metal & Glass
Dimensions (mm)	270x270x1500
Lamp Base	E27
Wattage	1x20W Max*
Lumen/CCT	-

Voltage: 220V / 50 Hz / 50-60 Hz | \*Bulb excluded. Recommended to be used with filament bulb





# Lustre



Model No. 41058



Model No. 41058



Model No. 41058



Model No. 41058

## See the bells shine

The Lustre collection makes an eye-catching addition to your space. With its shade akin to an inverted wine glass in high shine metallic paint, this easy to install light casts a focused beam for that added impact.

- Uniform finish for lustre and shine
- Adjustable height
- Easy installation

	Pendant	Pendant	Pendant	Pendant
Model No.	41058	41058	41058	41058
Colour	Gold	Chrome	Black	Copper
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	130x130x1500	130x130x1500	130x130x1500	130x130x1500
Lamp Base	E27	E27	E27	E27
Wattage	1x10W Max*	1x10W Max*	1x10W Max*	1x10W Max*
Lumen/CCT	–	–	–	–

Voltage: 220V/50Hz | \*Bulb excluded. Recommended to be used with Hue WA and WACA Bulb



# Vintage Cord



Model No. 31452



Model No. 31451

## Lights up the corners of your mind

Experience the old world rustic charm with efficacy of the modern LED filament bulbs. These minimal pendants are perfect for creating ambiance at a get together or lighting up a corner.

- Ideal for filament lamps
- Premium vintage-style finish
- Adjustable 1.5 meter cord
- Fits perfectly into any space

	Vintage Cord	Vintage Cord
Model No.	31451	31452
Colour	Rose Gold	Brushed Bronze
Material	Metal	Metal
Dimensions (mm)	140x140x1600	140x140x1600
Lamp Base	E27	E27
Wattage	1x20W Max*	1x20W Max*
Lumen/CCT	-	-

\*Bulb excluded. Recommended to be used with filament bulb





# Summit, Crown & Willow



Model No. 581896



Model No. 581900



Model No. 581899

## Shine from the top

Ceiling light are ideal for each section in your home. Light up your space with our wide range of decorative ceiling lamps that are available in different design, size and colour to fit your style and needs!

- High quality diffuser for uniform light effect.
- Robust metal construction.
- Perfect finish
- Long life LED light source

	Ceiling Lights	Ceiling Lights	Ceiling Lights
Model No.	581898	581899	581900
Colour	Silver	Silver	White & Wood Brown
Material	Aluminium	Aluminium	Metal & Wood
Dimensions (mm)	Dia. 400x100	Dia. 360x100	Dia. 350x150
Lamp Base	LED	LED	LED
Wattage	1x25W*	1x22W*	1x22W*
Lumen/CCT	2300lm/3000K/6500K	1450lm/3000K/6500K	900lm/3000K/6500K

\*Bulb not included. Recommended to be used with Hue WA and WACA Bulb





# WALL LIGHTS

Decorative wall lights are as essential to Indian homes as the home themselves. The choice of decorative wall is an extension of the overall décor and design language that the house stands to convey. A great wall light not only complements but also elevates the entire milieu and mood of the house.

Philips has a vast collection of wall lights for all moods and designs.

Have a look at the range and you would definitely pick one for your abode.



# Trunk & Tale



Model No. 31453



Model No. 31454



Model No. 31457



Model No. 31458

## The art of entertainment

We proudly present an all new range of decorative wall lights. These wall lights are inspired from eclectic sources and draw design inspiration from things that are common place yet inspire us and make every day a special day, one that is to be looked forward to. Pair these wall lights with our Hue bulbs and get that added zing to everyday activities whether that be entertainment or getting you more productive at things which matter-read, relax, concentrate, and energize.

- Clean contemporary design
- Fits perfectly into any home
- Beautiful glass & glossy finish

	Single Head Wall Light	Double Head Wall Light	Single Head Wall Light	Double Head Wall Light
Model No.	31453	31454	31457	31458
Colour	White & Silver	White & Silver	White & Black	White & Black
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	100x126x201	246x121x202	102x168x184	286x166x180
Lamp Base	E27	E27	E27	E27
Wattage	1x20W Max	2x20W Max	1x20W Max	2x20W Max
Lumen/CCT	–	–	–	–

Voltage: 220V / 50 Hz | \*Bulb excluded. | Recommended to be used with Hue WA and WACA Bulb





Model No. 31455

# Chiffe, Labyrinth & Totem



Model No. 31455



Model No. 31456



Model No. 31459

## Relax, focus, celebrate – turn every moment special

These wall lights are inspired from eclectic sources and draw design inspiration from things that are common place yet inspire us and make every day a special day, one that is to be looked forward to. Pair these wall lights with our Hue bulbs and get that added zing to everyday activities whether that be entertainment or getting you more productive at things which matter - read, relax, concentrate, and energize.

- Clean contemporary design
- Fits perfectly into any home
- Premium material
- Beautiful glass & glossy finish

	Single Head Wall Light	Double Head Wall Light	Single Head Wall Light
Model No.	31455	31456	31459
Colour	White & Silver	White & Silver	White
Material	Metal	Metal	Metal
Dimensions (mm)	100x125x200	251x127x203	154x82x322
Lamp Base	E27	E27	E27
Wattage	1x20W* Max	2x20W* Max	1x20W* Max
Lumen/CCT	–	–	–

Voltage: 220V, 50 Hz | \*Bulb excluded. | Recommended to be used with Hue WA and WACA Bulb





# Platina, Glint & Blush



Model No. 58184



Model No. 58070



Model No. 58185



Model No. 58185

## Design the perfect ambience

Experience easy maintenance with a relaxing aura and a touch of class with this wall light collection. The stainless steel base over a predominant frosted glass gives you perfect ambience with minimalist design.

- Expressive and elegant form
- Mirror finish for superior feel
- Classic Indian appeal

	Single Head Wall Light	Single Head Wall Light	Single Head Wall Light	Double Head Wall Light
Model No.	58184	58070	58185	58185
Colour	Shiny stainless steel base & glass opal paint finish			
Material	Stainless Steel	Stainless Steel	Stainless Steel	Stainless Steel
Dimensions (mm)	125x150x240	125x150x240	115x120x255	270x130x250
Lamp Base	E27	E27	E27	E27
Wattage	1x20W* Max	1x20W* Max	1x20W* Max	2x20W* Max
Lumen/CCT	–	–	–	–

Voltage: 220V, 50 Hz | \*Bulb excluded. | Recommended to be used with Hue WA and WACA Bulb



# Grace, Stylo & Trendo



Model No. 34303



Model No. 34304



Model No. 34302

## In the spotlight

Bring style into your house in brilliant matt chrome. Always be under the spotlight with these premium metal and synthetic decorative light that comes in 3 different types.

- Easy to maintain
- Designed for energy saving lamps
- Bright without a glare
- Soft indirect lighting

	Single Head Wall Light	Single Head Wall Light	Double Head Wall Light
Model No.	34302	34303	34304
Colour	White	White	White
Material	Metal	Metal	Metal
Dimensions (mm)	270x130x310	210x125x360	225x325x280
Lamp Base	B22d	B22d	B22d
Wattage	1x20W* Max	1x20W* Max	2x20W* Max
Lumen/CCT	-	-	-

Voltage: 220V, 50 Hz | \*20W Bulb excluded. | Recommended to be used with Hue WA and WACA Bulb





# Duo LED Wall Light



Model No. 58152



Model No. 58153



Model No. 58154



Model No. 58156



Model No. 58155

## Complement your abode

Made for illuminating walls, the Philips Duo wall light arches gracefully over your favourite wall & creates unique ambiance through the two light sources combined in one fixture. The energy efficiency and long-lasting performance are other definite advantages.

- Superior illumination
- Perfect finish
- Highlight the indoors
- Robust metal construction
- Long life LED light source

	Single Head Wall Light	Double Head Wall Light	Single Head Wall Light	Double Head Wall Light	Single Head Wall Light
Model No.	58152	58153	58154	58155	58156
Colour	White	White	White	White	White
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	160x152x228	378x152x228	120x120x118	270x100x119	410x135x66
Lamp Base	LED	LED	LED	LED	LED
Wattage	10W	20W	10W	20W	15W
Lumen/CCT	500lm/3000K	1000lm/3000K	700lm/3000K	1400lm/3000K	800lm/3000K

Voltage: 220-240V







# Oriel Next



Model No. 34141



Model No. 34142



Model No. 34143

## Mood Lighting for brighter days and warm evenings

Powered by the VariLume technology, this modern LED integrated fixture has everything to cover your requirements. Slim design, antique finish, and dual light mode for brighter days and warm evenings.

- Dual light mode
- Vibrant light pattern
- Slim design
- Long life LED source
- BIS safety standards registered

	Wall Light	Wall Light	Wall Light
Model No.	34141	34142	34143
Colour	Bronze	Bronze	Bronze
Material	Metal	Metal	Metal
Dimensions (mm)	317x120x35	317x120x35	317x120x35
Lamp Base	LED	LED	LED
Wattage	15W/6W	15W/6W	15W/6W
Lumen/CCT	800lm/300lm/3000K	800lm/300lm/ 3000K	800lm/300lm/3000K

Voltage: 220V-240V~, 50Hz | Warm White 3000K with good Color rendering (CRI-80)



# Bedside Lights



Model No. 30975



Model No. 48042



Model No. 31437



Model No. 48042

## Beautiful bedside lights

Reading in bed just got easier with this collection of adjustable LED bedside lights. Whether your décor matches white, black or chrome, our selection has you covered.

- Easy to adjust
- Gooseneck arm
- Long life LED light source
- Premium material & finish
- Energy saving

	Bedside Light	Bedside Light	Bedside Light	Bedside Light
Model No.	30975	48042	48042	31437
Colour	Grey	White	Black	White
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	470x67x28	500x90x90	500x90x90	151x151x78
Lamp Base	LED	LED	LED	LED
Wattage	2W	3W	3W	7W
Lumen/CCT	50lm/3000K	75lm/3000K	75lm/3000K	400lm/3000K

Voltage: 220-240V~, 50Hz. | \*Bulb excluded. | Recommended to be used with Hue WA and WACA Bulb





# Picture Light



Model No. 30973



Model No. 31440

## Entertainment is on the walls

Some places in our homes are insipid and unimaginative. These modern aluminum lights turn every space into a canvas. Full of ideas, these artistic lights will fill your head with a string of ideas. Whether it is the study room, bathroom or the kitchen, you'll see of these boring places in a new light.

- Flexibility to direct light
- Long life LED light source
- Premium material & finish

	Picture Light	Picture Light	Picture Light
Model No.	31440 / 31441	30973	48043
Colour	Chrome / Silver	Silver	Chrome
Material	Aluminum	Aluminum	Aluminum
Dimensions (mm)	500x180x95	350x70x87	500x70x95
Lamp Base	LED	LED	LED
Wattage	12W	6W	10W
Lumen/CCT	420lm/3000K	370lm/3000K	700lm/3000K





# Ultron Scene Switch Plus, Ultron Wall Light



Model No. 48027



Model No. 36283

## Elegance on your wall, lighting as you like it.

The slim and modern design of Ultron is a visual relief from usual linear products. These uniquely designed products have multiple applications - below cabinets, beneath shelves.

- Premium material and finish
- Long life LED source

	Wall Light	Wall Light	Wall Light
Model No.	48027	48027	36283
Colour	Grey CW	Grey CW	Grey CW/CDL/WW
Material	Synthetic	Synthetic	Synthetic
Dimensions (mm)	525x25x36	525x25x36	525x25x36
Lamp Base	LED	LED	LED
Wattage	17W	17W	24W
Lumen/CCT	1350lm/6500K	1350lm/6500K	2400lm 3000K/4000K/ 6500K

Voltage: 220V-240V~, 50Hz



# Trunk Linea



Model No. 31091



Connection wire  
31089



Connection  
31090

## Going the distance

A good replacement to the traditional T5 batten and with up to 20,000 hours lifetime, this white synthetic Philips myLiving Linea LED trunk batten is easy to install.

- Flexible and customisable
- Driver included

	Cove light	Cove light	Cove light
Model No.	31091   31094   31097	31092   31094   31098	31093   31094   31099
Colour	White	White	White
Material	Synthetics	Synthetics	Synthetics
Dimensions (mm)	–	–	–
Lamp Base	LED	LED	LED
Wattage	13W*	7W*	4W*
Lumen/CCT	1000lm/ 3000K/4000K/6500K	500lm/ 3000K/4000K/6500K	250lm/ 3000K/4000K/6500K

\* Included. Voltage: 220-240V





# Algebra



Model No. 31169



Model No. 31168

## Light and relaxed

High lumen decorative battens to give you neat and bright walls. A visual break from usual battens. These lights provide right lumen for all daily activities and stay on the wall as modern decorative fixtures.

- Bright light with uniform distribution
- Long life LED source
- Easy installation

	Wall/Ceiling Light	Wall/Ceiling Light
Model No.	31169	31168
Colour	White	White
Material	Synthetic	Synthetic
Dimensions (mm)	500x400x95	600x70x43
Lamp Base	LED	LED
Wattage	55W	27W
Lumen/CCT	6500K	2000lm/6500K

Voltage: 220V-240V, 50Hz







# Desk Lights



Model No. 61013



Model No. 61013



Model No. 31439



Model No. 581931



Model No. 31438

## Lighten up your reading moments

Perfect combination of task and ambient lighting. The direct lighting takes care of your bedside reading, while the ambient lighting in the table base ensures just the right visibility for comfortable and relaxed sleep. White matt finish blends in the background and does its job silently and effectively.

- Elegance meets dual function
- Convenience at your fingertips
- Separate on/off switches for both lights
- Ideal for reading
- Adjustable head for better beam & focus

	Breeze	Vector	AIR	SKYY	Hint
Model No.	61013	31439	61013	581931	58156
Colour	White	Carbon black	Carbon black	White	White
Material	Synthetic	Synthetic	Synthetic	Synthetic	Metal
Dimensions (mm)	270x135x370	140x140x480	270x135x370	253x379x396	151x105x450
Lamp Base	LED	LED	LED	LED	LED
Wattage	5W	5W	5W	5W	7W
Lumen/CCT	250lm/6500K	450lm/6500K	250lm/6500K	400lm/6500K	400lm/3000K

Voltage: 220V / 50 Hz





# DOWNLIGHTERS

Bring out the best in your home with the Philips range of Downlighters.

Equipped with the latest LED technology and designed for excellence in performance and quality, Philips downlighters are the perfect blend of innovation and modern design. Philips downlighters offer energy-saving benefits of LED, good light quality and maintenance free operation.





# Deco COB



Rose Gold



Black



Silver



Chrome

## Enhances the décor

- Minimalistic outer trim & deep recessed COB
- Focused 36 degree beam angle
- Longer life with 35,000 hours life
- Super robust construction - wide voltage protection from 160V-360V and surge up to 2KV
- Metal housing for longer life
- No harmful UV radiation, CRI>80
- BIS compliant; 2 years warranty

	LED Spot Light	LED Spot Light
Colour	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium
Dimensions (mm)	76x76x64	86x86x75
Cutout Dia (mm)	66	76
Wattage	7W	12W
Lumen/CCT	560lm/3000K/4000K/6500K	960lm/3000K/4000K/6500K

Voltage: 220-240V







# Thin Trim Deep Recessed COB



## The elegant face of illumination

- Minimalistic outer trim & deep recessed COB
- Focused 36 degree beam angle
- Longer life with 25,000 hours
- Super robust construction - Wide voltage protection from 160V-360V and surge up to 2KV
- Metal housing for longer life
- No harmful UV radiation, CRI>80
- BIS compliant; 2 years warranty

	LED Dimmable Spot Light	LED Dimmable Spot Light	LED Spot Light	LED Spot Light	LED Spot Light
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	55x55x100	75x75x100	55x55x100	75x75x100	92x92x120
Cutout Dia (mm)	52	68	52	68	68
Wattage	7W	12W	7W	12W	18W
Lumen/CCT	350lm/3000K/ 4000K/6500K	760lm/3000K/ 4000K/6500K	410lm/3000K/ 4000K/6500K	840lm/3000K/ 4000K/6500K	1260lm/3000K/ 4000K/6500K

Voltage: 220-240V



# Surface COB



## Focused surface light for your home & shop

- Brighter light output with 85 lm/w
- Premium aluminium material for better heat dissipation and endurance
- Uniform light output over product life of 20,000 hours
- No visible flickering, no UV/IR and low glare to prevent eye strain
- Surge protection of 2 KV with wide voltage protection 160-360V
- No harmful UV radiation, CRI>80
- Available in 7W, 12W and 18W CCTs of 6500K, 4000K & 3000K in round shape
- BIS compliant; 2 years warranty

	Surface COB	Surface COB	Surface COB
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	50x50x90	70x70x127	90x90x140
Cutout Dia (mm)	–	–	–
Wattage	7W	12W	18W
Lumen/CCT	585lm/ 3000K/ 4000K/6500K	1020lm/ 3000K/ 4000K/6500K	1530lm/ 3000K/ 4000K/6500K

Voltage: 220-240V





4 YEARS  
FREE  
CREDIT  
on everything in store



# COB Pro



## Express elegance beautifully

- Super bright light spectrum
- Delivers: 90lm/watt
- Focused 36 degree adjustable beam
- Longer life with 35,000 hours
- Super robust construction
- Wide voltage protection from 160V–360V and surge protection up to 2KV
- Premium white aluminium housing
- No harmful UV radiation

	LED Spot Light	LED Spot Light	LED Spot Light	LED Spot Light
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	90x90x50	105x105x52	120x120x65	120x120x80
Cutout Dia (mm)	81	95	110	110
Wattage	7W	12W	18W	22W
Lumen/CCT	630lm/3000K/ 4000K/6500K	1080lm/3000K/ 4000K/6500K	1620lm/3000K/ 4000K/6500K	1980lm/3000K/ 4000K/6500K

Voltage: 220-240V







# Aura StylEdge Downlighter



## Light with style

- Ultra thin rim for a seamless fit with decorative silver ring for beautiful aesthetics
- High lumen efficiency of upto 96lm/watt
- Designed for robustness: wide voltage protection from 160V-360V
- Surge protection up to 2KV
- Metal housing: good performance on high temperature and heat resistance
- Available in 5W, 7W, 10W & 15W in round shape only

	LED Downlighter	LED Downlighter	LED Downlighter	LED Downlighter
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	87x87x45	110x110x47	121x121x47	150x150x47
Cutout Dia (mm)	78	100	110	137
Wattage	5W	7W	10W	15W
Lumen/CCT	450lm/3000K/ 4000K/6500K	620lm/3000K/ 4000K/6500K	900lm/3000K/ 4000K/6500K	1420lm/3000K/ 4000K/6500K

Voltage: 220-240V



# DuraSlim

105lm  
per watt\*



## Slimmest metal panel with 35k life hours!

- Premium aluminium housing with unique slim design
- Longer life of 35k hrs
- Only 10mm thin
- Extra bright light with 105 lm/watt
- Surge protection of 2 KV with wide voltage protection 160-360V
- No visible flickering, no UV/IR and low glare to prevent eye strain
- Even and comfortable light perfected for your eye comfort
- Available in 5 wattages of 7W/12W/15W/18W/22W
- 6500K/4000K and 3000K CCTs in round/square form factor

	LED Downlighter	LED Downlighter	LED Downlighter	LED Downlighter	LED Downlighter
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	R: 120x120x10 S: 110x110x10	R: 160x160x10 S: 140x140x10	R: 180x180x10 S: 170x170x10	R: 20x200x10 S: 180x180x10	R: 225x225x10 S: 225x225x10
Cutout Dia (mm)	R: 105 S: 95	R: 145 S: 120	R: 165 S: 152	R: 185 S: 162	R: 208 S: 208
Wattage	7W	12W	15W	18W	22W
Lumen/CCT	735lm/3000K/ 4000K/6500K	1260lm/3000K/ 4000K/6500K	1575lm/3000K/ 4000K/6500K	1890lm/3000K/ 4000K/6500K	2310lm/3000K/ 4000K/6500K

Voltage: 220-240V





# CeilingSecure Ambiance Plus



## Choose colour style as per your preference!

- A Twist & Fit downlight that won't damage your false ceiling!
- 3 tunable white light modes to match your needs
- Relax/Show off: When you want to relax with family or when you entertain guests
- Everyday activities: Natural White when you want to watch TV or kids want to play
- Productivity: Cool Day Light when you want to read or kids want to study
- Controlled with any wall switch
- Available in 9W & 14W, round

	LED Downlighter	LED Downlighter
Colour	WW/CDL/NW	WW/CDL/NW
Material	Poly Carbonate	Poly Carbonate
Dimensions (mm)	132x132x83	162x162x83
Cutout Dia. (mm)	115	145
Wattage	9W	14W
Lumen/CCT	720lm/3000K/4000K/6500K	1120lm/3000K/4000K/6500K





# Slim Surface Mount+/ Surface Mount+



## A sleeker, slimmer, metal surface mount ceiling light


- Die-cast premium aluminium material for reliable performance
- Even and comfortable light perfected for your eye comfort
- No visible flickering, no UV/IR and low glare to prevent eye strain
- Surge protection of 2 KV with wide voltage protection 160-360V
- Improved lumen (80lm/w)
- Life of 35,000 hours over 1st Gen
- BIS safety standard, IEC 60598 registered and tested for 35° Ta

	LED Surface Downlighter	LED Surface Downlighter	LED Surface Downlighter	LED Surface Downlighter
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	R: 90x90x35 S: 90x90x35	R: 164x164x30 S: 144x144x30	R: 187x187x30 S: 181x181x30	R: 235x235x46 S: 230x230x46
Cutout Dia. (mm)	–	–	–	–
Wattage	3W	12W	15W	22W
Lumen/CCT	190lm/3000K/ 4000K/6500K	920lm/3000K/ 4000K/6500K	1200lm/3000K/ 4000K/6500K	1840lm/3000K/ 4000K/6500K

Voltage: 220-240V



# Linea Sharp



## Brighter light, longer life

- Strong focused 40° beam
- Wide voltage tolerance 160V-360V
- Glare free - easy on the eye

	LED Spotlight	LED Spotlight	LED Spotlight	LED Spotlight	LED Spotlight
Colour	WW/NW	WW/NW	WW/NW	WW/NW	WW/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	45x45x49	75x45x49	147x45x49	280x45x49	413x45x49
Cutout Dia (mm)	37x37	66x36	139x36	271x36	403x36
Wattage	3W	6W	10W	20W	30W
Lumen/CCT	150lm/ 3000K/4000K	525lm/ 3000K/4000K	700lm/ 3000K/4000K	1400lm/ 3000K/4000K	2100lm/ 3000K/4000K





# LuminAir



929002597001



929002597002



## A fan so brilliant it will light up your home


Experience the best of powerful performance and noise-less efficiency. Our BLDC technology with brushless motor ensures smooth operation across a wide range of voltage fluctuations, while controlling speeds conveniently with remote and saving 50% energy.

- Quiet operation less noise
- BLDC motor for longer life
- No external regulator required
- Wide voltage and surge protection

	Ceiling Fan Crystal	Ceiling Fan Silver
Model No.	929002597001	929002597002
Colour	Cool White   Natural White   Warm White	Cool White   Natural White   Warm White
Material	Crystal	Silver
Wattage	75W	75W







# COVER LIGHTING


Philips LED strip lights is an innovation in customizable home illumination for the perfect ambiance to your liking. Unlike fluorescent tubes, flexible LED strip lights can be curved around corners, trimmed and connected to any required length.

Take your creativity off the straight and narrow, and experiment in exploring new ways to use to LED strip lights.



# Linea Bright/Premium/ Blue & Pro Glow

500lm  
per Mtr<sup>\*</sup>



900lm  
per Mtr<sup>\*</sup>



900lm  
per Mtr<sup>\*</sup>



## Turn any ambience perfect

Express yourself with the Philips Cove lighting. This flexible LED tape is perfect behind furniture or along ceiling coves, giving you all true shades of white.

- High quality LED for bright and true shades of white
- Flexible and customisable
- Superior adhesive for easy installation

	Cove Light	Cove Light	Cove Light	Profile Strip Light
Colour	WW/CDL/NW	WW/CDL/NW	Blue	WW/CDL/NW
Material	NA	NA	NA	NA
Dimensions (mm)	5000x8x0.3 (5 mtrs.)	5000x8x0.3 (5 mtrs.)	5000x8x0.3 (5 mtrs.)	5000x10x0.2
No. of LEDs	720 LED/mtr	60 LED/mtr	60 LED/mtr	240 LED/mtr
Wattage	28W with driver	50W LED with driver	25W LED with driver	45W with driver
Lumen	2400lm for 5 mtr	4500lm for 5 mtr	-	900lm/mtr

Voltage: 220-240V







# SPOTLIGHT

Spots are a great addition to your indoor home lighting. They do multiple jobs of wall washing a highlighted area or focusing light source for some specific purposes like reading or just being there as a decorative fixture.

Philips offers spotlights in many designs and finishes. The range keeps expanding all the time.





# Nixon



Model No. 581919



Model No. 581919



Model No. 581920

## Bring every moment in focus

These wall lights are inspired from eclectic sources and draw design inspiration from things that are common place yet inspire us and make every day a special day, one that is to be looked forward to.

- Modern design for elegant look
- Long life LED light source
- Robuts metal construction
- Adjustable head with swivel joint

	LED Wall Light	LED Wall Light	Double Head LED Wall Light
Model No.	581919	581919	581920
Colour	White	Chrome	Chrome
Material	Metal	Metal	Metal
Dimensions (mm)	115x115x125	115x115x125	295x65x140
Lamp Base	LED	LED	LED
Wattage	7W	7W	10W
Lumen/CCT	350lm/3000K	350lm/3000K	550lm/3000K



# Star & Burlap Nickel



Model No. 56240



Model No. 50230

## Accent your home with light

This light collection speaks of timeless elegance with its high quality chrome finish. It gives an elegant and classic look to your living room.

- High quality chrome finish
- Available in single and multi-head configuration
- Adjustable head

	Single Spot Light	Single Spot Light
Model No.	56240	50230
Colour	White	White & Chrome
Material	Aluminum	Synthetic, Metal
Dimensions (mm)	118x82x60	80x180x130
Lamp Base	LED	E14
Wattage	4W	40W*
Lumen/CCT	230lm	–

Voltage: 220-240V \* Not Included





Model No. 581879



Model No. 581881



Model No. 581880

# Aspire & Vista



Model No. 581879



Model No. 581881



Model No. 581880

## Accentuate your lifestyle

The best choice for modern homes. Modern simplistic design brings about a unique functionality to the product without compromising on design and areas of the home which extend from bedroom to living to kitchen and aesthetics. This well designed product can be used for multiple applications and many more.

- Perfect finish
- High quality construction
- Adjustable head

	Single Spot Light	Double Spot Light	Vista Wall
Model No.	581879	581880	581881
Colour	White	White	White
Material	Metal	Metal	Metal
Dimensions (mm)	110x110x113	320x110x113	134x134x144
Lamp Base	GU 10	GU 10	E14
Wattage	1x50W Max	2x50W Max	1x40W Max
Lumen/CCT	-	-	-

Voltage: 220V / 50 Hz | \*Bulb excluded. | Recommended to be used with Hue WA and WACA Bulb







# BATHROOM

Bathroom and kitchen are most involved and intimate spaces in your house. Recreating these spaces with right quality of light and using right form factor for light is extremely important for harmony and wellbeing of the entire family.

The right colour elevates sensory experiences and creates true delight for all. Right form factor ensures that visual fatigue is kept to minimum and space looks light and cheery.



# Atom & Poise



Model No. 581922



Model No. 581915

## Easy on the eye, light on the senses

Want shiny teeth and complexion? Then you'll need to be able to see yourself in the best light. This Philips range is just right for your bathroom with IP44 moisture protection, a reduced glare, premium opal glass housing and chrome mount for a mirror finish.

- Designed for humid environment
- Premium glass for reduced glare
- Long life LED light source
- Robust metal construction
- Adjustable head with swivel joint

	LED Wall Light	LED Wall Light
Model No.	581922	581915
Colour	Chrome	Chrome
Material	Metal	Metal
Dimensions (mm)	140x140x125	175x175x120
Lamp Base	LED Integrated	LED Integrated
Wattage	7W	6W
Lumen/CCT	350lm/3000K	210lm/3000K

Voltage: 240V/50 Hz.





# Majesty



Model No. 581918

## Add the style, enhance the clarity

It takes more than soap and water to keep a person well groomed. Choose this range for a bright and shiny look for yourself and your bathroom. This coordinated range provides maximum clarity with minimal glare and is just right for your bathroom with IP44 moisture protection, a premium opal glass housing and chrome mount for a mirror finish.

- Robust metal construction
- Designed for humid environment
- Adjustable head with swivel joint
- Premium glass for reduced glare
- Long life LED light source

	Ceiling Light
Model No.	581918
Colour	Chrome
Material	Metal
Dimensions (mm)	500x500x95
Lamp Base	LED Integrated
Wattage	27W
Lumen/CCT	2300lm/3000K



Model No. 581915



# Jojoba



## Perfect harmony

Duality, despite being made of two distinct elements can coexist and complement each other – and this wall light does just that.

- Silver finish for modern look
- High quality synthetics for long lasting durable shine
- Weather proof with IP44 rating

	Wall Light
Model No.	34034
Colour	Silver
Material	Synthetics
Dimensions (mm)	300 x107x52
Lamp Base	LED Integrated
Wattage	7.5W
Lumen/CCT	450lm/4000K

Voltage: 220V-240V, 50Hz | \*Bulb excluded



# Aquila & Vega



Model No. 58157



Model No. 58158

## Light and relaxed

The aesthetic design with chrome finish & bright output of Aquila & Vega will boost the look of every mirror and stay on the wall as modern decorative fixtures.

- Superior illumination
- Polished chrome finish
- White glass shade
- Optimum performance

	Wall Light	Wall Light
Model No.	58157	58158
Colour	Polished chrome finish	Polished chrome finish
Material	Metal	Metal
Dimensions (mm)	395x105x140	595x105x140
Lamp Base	LED Integrated	LED Integrated
Wattage	15W	22W
Lumen/CCT	1275lm/3000K	2000lm/3000K





# Mirror



Model No. 31165



Model No. 31167

## Bright mirrors and brighter moods

High lumen decorative battens to give you neat and bright walls. A visual break from usual battens.


These lights provide right lumens for all daily activities and stay on the wall as modern decorative fixtures.

- Flexible head to direct lights where needed (31167 only)
- Dual diffuser reduce glare
- Long lasting LED source

	Wall Light	Wall Light
Model No.	31165	31167
Colour	White	White
Material	Synthetic & Aluminium	Synthetic & Aluminium
Dimensions (mm)	55x539x38	36x552x76
Lamp Base	LED	LED
Wattage	11W	11W
Lumen/CCT	800lm	800lm







# TRACK LIGHT

Be it public spaces or private homes, Track Lights offer an efficient and elegant way to illuminate your spaces - anytime of night or day.

Philips offers a range of versatile Track Lights that are easily installable on ceiling or wall mounted fixtures, and offer a tasteful approach to illumination.

Be it the relaxing glow of 'warm lighting' for intimate home moments, or the energetic spark of 'cold lighting' to enhance retail ambiances and experiences - the Philips Track Light range delivers the best of style, performance and value.



# Track Light



Model No. 31445



Model No. 31446



Model No. 31447



Model No. 31448



## Reimagine retail

There's more to things than meets the eye, Philips track light range is a must for every retail outlet which will not only enhance the product appearance but take it from usual to the ultimate best.

- Customizable wattage options
- Long-lasting fixture
- Robust metal construction
- Functional, minimal design
- Perfect fit for any home/outlet

	Track Head	Track Head	Track Head	Track Head
Model No.	31445	31446	31447	31448
Colour	Black	Black	Black	Black
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	180x50x110	158x65x125	165x82x154	122x68x130
Lamp Base	LED	LED	LED	GU10
Wattage	10W	20W	30W	1x10W Max*
Lumen/CCT	700lm/3000K	1500lm/3000K	2150lm/3000K	–

\* Not Included







# OUTDOOR

Other than the functional requirements of lighting and security, Outdoor lighting truly goes beyond illumination. Outdoor lighting defines the silhouette of the home, the very character of it.

The right combination of design and placement can elevate and take the outdoor experience to an entire next level. The texture and vibrancy of the walls, the garden and the greenery, the fountain and everything else can be accentuated with the wide variety of archetypes available.

Philips lifestyle offers widest variety of Outdoor collection in all design languages. The lasting look and performance of these luminaires are a testimony of great design, sturdy build, and impeccable finish.





# Samondra, Actea, Petronia & Drosera



Model No. 1739193



Model No. 1739030



Model No. 1739493



Model No. 1739330

## Cast a warm glow

These outdoor wall lights are fashioned from durable, high quality colour. The familiar pillbox design casts a powerful, diffused, warm white light in all directions for clear illumination in outdoor areas.

The minimal clean cut design ensures easy maintenance and cleaning of the fixtures.

- Cozy light effect
- Moisture resistance
- High quality finish

	Wall Light	Wall Light	Wall Light	Wall Light
Model No.	1739193	1739030	1739493	1739330
Colour	White & Black	Black	White & Black	White & Black
Material	Synthetic, Metal	Synthetic, Metal	Synthetic, Metal	Synthetic, Metal
Dimensions(mm)	190.1x89.5x190.1	189x189x74	190.1x53x190.1	190.1x73.7x190.1
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	12W	12W	12W	12W
Lumen/CCT	1200lm	1200lm	1200lm	1200lm

Voltage: 220-240V



# Kiskadee, Serres, Astilbe & Cormorant



Model No. 1738393



Model No. 1738930



Model No. 1738030



Model No. 1738130

## Illuminate your outdoors

These outdoor wall lights are fashioned from durable, high quality colour. The familiar pillbox design casts a powerful, diffused, light in all directions for clear illumination in outdoor areas.

These elegant pieces have clean lines with very strong accents. Perfect for a contemporary garden.

- High quality material: resistant to corrosion, rust and stains in all weather conditions
- Synthetic diffuser

	Wall light	Wall Light	Wall Light	Wall Light
Model No.	1738393	1738930	1738030	1738130
Colour	White & Black	White & Black	White & Black	White & Black
Material	Synthetic, Metal	Synthetic, Metal	Synthetic, Metal	Synthetic, Metal
Dimensions (mm)	197x140x212	182x133x170	177.5x177.5x175.2	207x250x266
Lamp Base	E27	E27	E27	E27
Wattage	1x42W (Max)*	1x42W (Max)*	1x42W (Max)*	1x42W (Max)*
Lumen/CCT	–	–	–	–

Voltage: 220-240V. \*Not included





# Macaw, Caiques & Eagle



Model No. 17303



Model No. 17302



Model No. 17304

## Accentuate your exteriors

These modern, neatly done, regular shaped fixtures are complement for the modern home and outdoor. The simple perfect design not only makes these delightful but also easy on maintenance and cleaning.

- Designed for outdoor use - water resistant IP44
- High quality LED light

	Wall Light	Wall Light	Wall Light
Model No.	17303	17302	17304
Colour	Inox	Black	Black
Material	Aluminium, Synthetic	Aluminium, Synthetic	Aluminium, Synthetic
Dimensions (mm)	130x122x85	130x122x85	170x170x74
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	3.5W	3.5W	3.5W
Lumen/CCT	320lm	120lm	270lm

Voltage: 220-240V





# Gamma Light

IP65



Model No. 58159



Model No. 58160



Model No. 58161

## Designed to delight

These elegantly designed wall washers are a perfect draw out of the modern design. Soft corners and anthracite colour accentuate the gentle throw of the light in two directions. IP65 rating assures product usage both in interiors as well as exteriors.

- Superior illumination
- Classy anthracite finish
- Premium aluminium material
- Optimum performance
- Bi-directional beam
- IP65 fixture ideal for outdoor & wet areas

	Single Head Wall Washer	Double Head Wall Washer	Three Head Wall Washer
Model No.	58159	58160	58161
Colour	Anthracite	Anthracite	Anthracite
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	79x77x36	119x80x38	168x80x41
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	2W	4W	7W
Lumen/CCT	100lm/3000K	250lm/3000K	382lm/3000K


Voltage: 220-240V



Model No. 58162



Model No. 31450



Model No. 58163

# Alpha, Triangular & Propulsio

IP65



Model No. 58162



Model No. 31450



Model No. 58163

## Add charisma to your space

These elegantly designed wall washers are a perfect draw out of the modern design. Soft corners and anthracite colour accentuate the gentle throw of the light in two, three and four directions.

- Superior illumination
- Classy anthracite finish
- Premium aluminum material
- Optimum performance
- Highlight the outdoors
- IP65 fixture ideal for outdoor & wet areas

	Wall Washer	Wall Washer	Wall Washer
Model No.	58162	58163	31450
Colour	Anthracite	Anthracite	Anthracite
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	111x111x100	165x165x49	159x99x66
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	12W	9W	10W
Lumen/CCT	950lm/3000K	550lm/3000K	670lm/3000K

Voltage: 220-240V





# LED Wall Washer



Model No. 34153



Model No. 34153

## Transform the atmosphere

This elegantly designed wall washer is a perfect draw out of the modern design. Soft rounded corners and white colour accentuate the gentle throw of the light in both the directions. IP44 rating assures product usage both in interiors as well as exteriors.

- Long life LED source
- Bright warm white light

	Wall Washer	Wall Washer
Model No.	34153	34153
Colour	White	Anthracite
Material	Aluminium	Aluminium
Dimensions (mm)	153x108x73	153x108x73
Lamp Base	LED	LED
Wattage	7W	7W
Lumen/CCT	250lm/3000K	250lm/3000K

Voltage: 220V-240V, 50Hz



Model No. 58164



Model No. 31436



# Lima & Andromeda LED Steplight

IP65



Model No. 58164



Model No. 31435

## An urbane elevation

Clean cut, slim lines, and white matt finish make Andromeda a perfect choice for modern urban homes. The white matt finish while merging with the background also ensures an enduring neat look for a long time.

- LED light with beautiful light pattern
- Highlight the outdoors
- Endurance meets contemporary style
- Clean lines, sleek design, warm white light
- Robust finish

	Step Light	Step Light
Model No.	58164	31435
Colour	White	Anthracite grey
Material	Aluminium	Aluminium
Dimensions (mm)	100x100x40	104x104x35
Lamp Base	LED Integrated	LED Integrated
Wattage	3W	3W
Lumen/CCT	70lm/3000K	50lm/3000K

Voltage: 220-240V



# Step Light



Model No. 30974



Model No. 34151



Model No. 34152



Model No. 31436

## Step up the glam

The neatly designed modern and minimal steplight melds into the background settings and provides just the right ambient illumination to create an interesting setting.

- Long life LED source
- Bright warm white light

	LED Step Light	LED Step Light	LED Step Light	LED Step Light
Model No.	30974	34151	34152	31436
Colour	White	Anthracite grey	Anthracite grey	Anthracite grey
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	85x85x32	84x84x44	115x84x44	201x91x35
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	2W	2W	3W	5W
Lumen/CCT	30lm/3000K	30lm/3000K	85lm/3000K	165lm/3000K

Voltage: 220-240V







# Garden Spike

IP65



Model No. 31385



Model No. 31386

## Spike up the gorgeousness

The well-designed modern and rugged Garden Spike is a great addition to highlight your garden spaces. COB integrated lighting keeps the product high on light dispersion and efficiency.

- 80% energy savings
- Outdoor ambient lighting
- Protection against dust & jet of water from any direction
- IP65 fixture ideal for outdoor & wet areas

	Garden Spike	Garden Spike
Model No.	31385	31386
Colour	Anthracite	Anthracite
Material	Aluminium	Aluminium
Dimensions (mm)	100x75x75	122x85x85
Lamp Base	LED COB Integrated	LED COB Integrated
Wattage	7W	12W
Lumen/CCT	360lm/4000K	625lm/4000K

Voltage: 220-240V





# Glide

IP65



Model No. 58174



Model No. 58176



Model No. 58175

## Walk on the stylish side

The wonderful design of Glide is a stylish way to enjoy your outdoor moments. High-quality materials and classic finish fit perfectly with your personal style.

- Highlight the outdoors
- IP65 fixture ideal for gardens
- Black premium finish

	Wall Lantern	Post Lantern	Pedestal Lantern
Model No.	58174	58175	58176
Colour	Black	Black	Black
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	156x260x290	156x156x337	156x156x600
Lamp Base	E27	E27	E27
Wattage	1x9W Max	1x9W Max	1x9W Max
Lumen/CCT	–	–	–

Voltage: 220-240V



# Yolo & Blade

IP65



Model No. 58168



Model No. 58169



Model No. 58172



Model No. 58173

## Light up your path

Enjoy a beautiful garden with an IP 65 range of outdoor lights. This outdoor range is especially designed for harsh outdoor environments.

- LED light with beautiful light pattern
- Highlight the outdoors
- IP65 fixture ideal for gardens
- Black premium finish

	Wall Lantern	Pedestal Lantern	Wall Lantern	Pedestal
Model No.	58168	58169	58172	58173
Colour	Black	Black	Black	White & Black
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	90x125x265	85x85x800	90x125x200	85x85x500
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	9W	9W	9W	9W
Lumen/CCT	460lm/3000K	460lm/3000K	350lm/3000K	350lm/3000K

Voltage: 220-240V \* Not Included





# Pylon & Yob

IP65



Model No. 58170



Model No. 58171



Model No. 58167



Model No. 58166

## Outline the outdoors... stunningly.

Enjoy a beautiful garden with an IP 65 range of outdoor lights. This outdoor range is especially designed for harsh outdoor environments.

- LED light with beautiful light pattern
- Highlight the outdoors
- IP65 fixture ideal for gardens
- Black premium finish

	Wall Lantern	Pedestal Lantern	Wall Lantern	Pedestal
Model No.	58170	58171	58166	58167
Colour	Black	Black	Black	Black
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	90x125x200	85x85x650	100x110x137	195x195x650
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	9W	9W	5W	5W
Lumen/CCT	360lm/3000K	360lm/3000K	360lm/3000K	360lm/3000K

Voltage: 220-240V







# Robin



Model No. 15470



Model No. 15472



Model No. 15473

## Night long glow

An amazing fusion of form and function. Sculpted in heritage design while being detailed on modern lines, the range gives the outdoor spaces a contemporary touch.

Uniquely blended in anthracite color, the product stands out in outdoor setting. High quality integrated LEDs assure soothing warm white light all night long.


- Cozy light effect
- Moisture resistance
- High quality aluminum

	Wall Light	Pedestal Light	Post Light
Model No.	15470	15472	15473
Colour	Black	Black	Black
Material	Aluminium, Synthetic	Aluminium, Synthetic	Aluminium, Synthetic
Dimensions (mm)	174x200x240	174x174x335	174x174x855
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	8W	8W	8W
Lumen/CCT	430lm	430lm	430lm

Voltage: 220-240V



# Arbour



Model No. 16463



Model No. 16459



Model No. 16476

## Turn the outdoors magical

A cube of light in the cradle of durable die-cast Aluminum – this ingenious design casts magical warm white light over pathways and open areas outdoors.

The modern design and regular geometric form lends minimalist feel to the product. The unique design coupled with Philips reliability make up for a great outdoor fixture ideal for well-done contemporary houses and lawns.

- Design for outdoor use
- Durable housing
- High quality aluminium

	Wall Light	Pedestal Light	Post Light
Model No.	16459	16476	16463
Colour	Anthracite	Anthracite	Anthracite
Material	Aluminium, Synthetic	Aluminium, Synthetic	Aluminium, Synthetic
Dimensions (mm)	150x150x244	150x150x244	100x100x770
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	8W	8W	8W
Lumen/CCT	600lm	600lm	600lm

Voltage: 220-240V









# IP67

## All Weather In-Ground Lights



# IP65

## All Weather Surface Lights



### A weather-proof fixture!

Designed for harsh outdoor conditions of dust & water with IP67 rating. The product offers uniform light output ensuring best in class performance.

- An affordable inground light suitable for - gardens & patios, pool areas, other high-exposure areas
- IP67 rating means the fixture is protected in most types of weather (dust & rain + protected from temporary immersion in water)
- Diffused soft light: perfect for outdoor lighting & low on glare
- Able to handle surge protection up to 2 KV
- Dust-proof - No Ingress of dust

	LED Inground Light	LED Inground Light	LED Inground Light	LED Surface Light
Model No.	-	-	-	-
Colour	Grey	Grey	Grey	WW/CW
Material	Metal	Metal	Metal	Rust-free synthetic
Dimensions (mm)	55x55x90.6	65x65x92	75x75x103	205x205x54
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	3W	5W	10W	12W
Lumen/CCT	160lm	250lm	500lm	840lm

Voltage: 220-240V

Product Descriptions	MRP
<b>CHANDELIERS</b>	
581865 Caesar Wall Crystal SS G9 1*MAX 42W	7,200/-
581864 Caesar Pendant Crystal SS G9 6*MAX 42W	42,000/-
581863 Caesar Crystal SS G9 5*MAX 42W	39,000/-
581846 Corona Pendant Crystal SS Chrome G9 7*MAX 42W	39,000/-
581847 Corona Crystal SS Chrome G9 7*MAX 42W	34,200/-
581886 Corona Pendant Crystal SS Chrome G9 5*MAX 42W	50,000/-
581857 Monarch Chandelier Crystal Ag Al rod E14 6*MAX 60W	34,200/-
581858 Monarch Wall Crystal Ag Al rod E14 1*MAX 60W	6,240/-
581885 Monarch Chandelier Crystal Ag Al rod E14 9*MAX 60W	45,000/-
581842 Allure Pendant Crystal Chrome G9 5*MAX 42W	46,200/-
581843 Allure Crystal French Gold G9 4*MAX 42W	34,200/-
581845 Corral Chandelier Crystal SS G9 5*MAX 42W	29,400/-
581906 Chalice Chandelier Crystal Congac Glass SS G9 6*MAX 42W	35,990/-
581841 Chalice Chandelier Crystal Congac Glass SS G9 6*MAX 42W	33,000/-
581844 Crescent Pendant Crystal Ivory Gold G9 5*MAX 42W	39,000/-
581884 Crescent Pendant Crystal Chrome G9 5*MAX 42W	40,000/-
581849 Cameo Crystal SS Chrome G9 5*MAX 28W	24,000/-
581850 Cameo Crystal SS Chrome G9 5*MAX 28W	18,000/-
581903 Splendora Pendant Anodized Ag Al rod G9 7*MAX 42W	32,990/-
581904 Splendora Anodized Ag Al rod G9 7*MAX 42W	30,990/-
581905 Splendora Single Wall Anodized Ag Al rod G9 1*MAX 42W	6,990/-
581901 Torrent Pendant Clear Crystal SS G9 6*MAX 42W	54,900/-
581902 Torrent 1H WL Clear Crystal SS G9 1*MAX 42W	7,490/-
581861 Mushroom Crystal Chrome E14 G9 6*MAX 42W	55,000/-
581862 Mushroom Pendant Crystal Chrome E14 G9 6*MAX 42W	58,000/-
581853 Regalia Pendant Borosilicate Glass Chrome G9 12*MAX 42W	24,000/-
581852 Regalia Double Wall Clear Glass Chrome G9 2*MAX 42W	6,990/-
581851 Regalia Single Wall Glass Chrome G9 1*MAX 42W	4,590/-
581859 Blossom Pendant Glass Chrome E27 4*MAX 40W	34,200/-
581860 Blossom Glass Chrome E27 4*MAX 40W	39,000/-
581855 Adonis Pendant Vacuum Glass Red CU G9 10*MAX 28W	65,000/-
581856 Adonis Pendant Vacuum Glass Chrome G9 10*MAX 28W	62,000/-
581854 Umbra Pendant Borosilicate Glass Chrome & Red CU GG9 8*MAX 33W	36,000/-



Product Descriptions	MRP
<b>LEAD FAMILIES</b>	
40936 Outline Chandelier LED Bronze 1x36	40,600/-
40937 Outline Wall Lamp LED Bronze 1x9W	9,280/-
40938 Outline Table Lamp LED Bronze 1x9	13,920/-
40939 Outline Floor Lamp LED	16,240/-
58145 Jazz Wall Light Single	3,600/-
58145 Jazz Wall Light Double	5,900/-
58147 Jazz Pendant Single	5,050/-
58148 Jazz 3 Head Pendant	9,000/-
58149 Jazz Table Lamp	4,800/-
58150 Jazz Floor Lamp	7,800/-
58135 Roseate Wall Light Double	6,950/-
58135 Roseate Wall Light Single	4,100/-
58137 Roseate Pendant Single	6,950/-
58138 Roseate 3 Head Pendant	10,550/-
58139 Roseate Table Lamp	5,750/-
58140 Roseate Floor Lamp	9,500/-
31425 Muziris Single Head Wall Light	2,650/-
31426 Muziris Double Head Wall Light	4,450/-
31427 Muziris Conical Fabric Pendant	4,200/-
31428 Muziris Cylindrical Fabric Pendant	4,450/-
31433 Muziris Wood Pendant	4,800/-
31434 Muziris Laminar Wall Light	2,400/-
31429 Muziris 1 Head Cylindrical Pendant	2,400/-
31430 Muziris 3 Head Cylindrical Pendant	6,600/-
31431 Muziris 1 Head Gold Cylindrical Pendant	3,000/-
31432 Muziris 3 Head Gold Cylindrical Pendant	7,200/-
31402 Muziris 7W Picture Light	2,750/-
31403 Muziris 12W Picture Light	3,100/-
58071 Grandeur Wall Light Double	4,900/-
58071 Grandeur Wall Light Single	2,750/-
58072 Grandeur Pendant 3 Head Pendant	7,800/-
581871 Floret Single Wall Lamp	Coming Soon
581872 Floret Double Wall Lamp	Coming Soon

Product Descriptions	MRP
581873 Floret Table Lamp	Coming Soon
581876 Striker Single Wall Lamp	3,990/-
581877 Striker Table Lamp	3,990/-
581878 Striker Floor Lamp	7,800/-
581874 Sierra Floor Lamp Black 1* E27	8,000/-
581874 Sierra Floor Lamp White 1* E27	8,000/-
581875 Arc Floor Lamp White 1* E27	12,000/-
37932 Pendant Bronze 5x40W 230V	9,772/-
37934 Wall Lamp Bronze 1x40W 230V	2,600/-
PENDANTS & CEILING	
30898 Ceiling Lamp Chrome 4x42W 230V	17,980/-
30899 Pendant Chrome 4x42W 230V	23,345/-
40913/31/PN / Smart Volume Ring	8,500/-
40917/31/PN / Smart Volume Sandalwood	8,500/-
40950/31/PN / ECRU Ceiling Light	4,200/-
41231 Apollo Pendant White 1x10.5W 240V	7,200/-
58130 Panache Pendant Silver and Blue	5,900/-
58130 Panache Pendant Stainless Steel and White	6,250/-
58130 Panache Pendant Turtle Green and White	5,900/-
58074 Beacon Pendant Rose gold and Silver	3,850/-
58074 Beacon Pendant Wine and Silver	3,850/-
58125 Gleam Pendant Chrome	4,450/-
58125 Gleam Pendant Copper	4,550/-
58076 Blithe Pendant Wine And Silver	9,600/-
58076 Blithe Pendant Rosegold And Silver	9,600/-
58078 Blithe 3 Head Pendant Wine And Silver	7,800/-
58078 Blithe 3 Head Pendant Rosegold And Silver	7,800/-
58127 Tawny Pendent Copper	5,050/-
41058 Lustre Pendant Black 1x24W 230V	3,760/-
41058 Lustre Pendant Chrome 1x24W 230V	3,760/-
41058 Lustre Pendant Copper 1x24W 230V	3,132/-
41058 Lustre Pendant Gold 1x24W 230V	3,760/-
31451 Vintage Cord Rose Gold	1,250/-
31452 Vintage Cord Brush Bronze	1,250/-
581898 Summit Ceiling Light	Coming Soon

Product Descriptions	MRP
581899 Crown Ceiling Light	Coming Soon
581900 Willow Ceiling Light	Coming Soon
<b>WALL LIGHTS</b>	
31453 Trunk Wall Light 1H	3,100/-
31454 Trunk Wall Light 2H	5,900/-
31457 Tale Wall Light 1H	3,100/-
31458 Tale Wall Light 2H	5,900/-
31455 Chiffe Wall Light 1H	3,100/-
31456 Labyrinth Wall Light 2H	5,900/-
31459 Totem Wall Light	3,100/-
58184 Platina Wall Light - Single	3,000/-
58070 Glint Wall Light - Single	3,100/-
58185 Blush Wall Light - Double	5,400/-
58185 Blush Wall Light - Single	3,000/-
34303 Grace Wall Light - Single	1,300/-
34302 Stylo Wall Light - Single	1,200/-
34304 Trendo Wall Light - Double	2,150/-
58152 10W Duo Led Wall Light	4,300/-
58153 20W Duo Led Wall Light	7,700/-
58154 10W Duo Led Wall Light	3,950/-
58155 20W Duo Led Wall Light	5,500/-
58156 15W Duo Led Wall Light	4,300/-
34143 Oriel LED Wall Light- Jal Dim (WW)	3,000/-
34141 Oriel LED Dim Wall Light - Giraffe (WW)	3,000/-
34142 Oriel LED Dim Wall Light- Classic (WW)	3,000/-
30975 Bedside Light (3000K)	1,500/-
48042 Bedside Light (3000K)	1,950/-
48042 Bedside Light (3000K)	1,950/-
31437 Hint Bedside Light WH 30K	3,350/-
31440 Picture Lights 12W Chrome	2,700/-
31441 Picture Lights 12W Silver	2,700/-
30973 Picture Light LED 6W	2,400/-
Picture Light Chrome LED 10W 30K	2,750/-
48027 Ultron Scene Switch Plus	2,100/-
31091 Trunk Linea 3000K	850/-



Product Descriptions	MRP
31094 Trunk Linea 4000K	850/-
31097 Trunk Linea 6500K	850/-
31092 Trunk Linea 3000K	560/-
31095 Trunk Linea 4000K	560/-
31098 Trunk Linea 6500K	560/-
31093 Trunk Linea 3000K	390/-
31094 Trunk Linea 4000K	950/-
31099 Trunk Linea 6500K	390/-
31089 Trunk Linea Accessories	390/-
31169 Algebra	4,640/-
31168 Algebra	2,320/-
61013 Breeze Table Lamp	1,450/-
31439 Vector Table Lamp	1,100/-
61013 Air Table Lamp	1,450/-
581931 Skyy Table Lamp	Coming Soon
31438 Hint Table Lamp WH 30K	4,100/-
DOWNLIGHTERS	
Deco COB LED Spot Light 7W	2,200/-
Deco COB LED Spot Light 12W	2,750/-
Thin Trim Dimmable Deep Recessed 7W COB	1,810/-
Thin Trim Dimmable Deep Recessed 12W COB	2,145/-
Thin Trim Dimmable Deep Recessed 18W COB	3,625/-
Thin Trim Dimmable Deep Recessed 7W COB Dimmable	2,515/-
Thin Trim Dimmable Deep Recessed 12W COB Dimmable	3,020/-
Surface COB 7W	2,010/-
Surface COB 12W	2,750/-
Surface COB 18W	3,805/-
COB Pro LED Spot Light 7W	1,650/-
COB Pro LED Spot Light 12W	2,170/-
COB Pro LED Spot Light 18W	3,240/-
COB Pro LED Spot Light 22W	3,775/-
Aura StylEdge LED Downlighter 5W	1,305/-
Aura StylEdge LED Downlighter 7W	1,525/-
Aura StylEdge LED Downlighter 10W	1,845/-
Aura StylEdge LED Downlighter 15W	2,180/-

Product Descriptions	MRP
DuraSlim LED Downlighter 7W	1,125/-
DuraSlim LED Downlighter 12W	1,450/-
DuraSlim LED Downlighter 15W	1,800/-
DuraSlim LED Downlighter 18W	2,260/-
DuraSlim LED Downlighter 22W	2,835/-
CeilingSecure Ambience Plus LED Downlighter 9W	1,350/-
CeilingSecure Ambience Plus LED Downlighter 14W	1,680/-
Surface Mount+ LED Surface Downlighter 3W	1,115/-
Slim Surface Mount+ LED Surface Downlighter 12W	1,945/-
Slim Surface Mount+ LED Surface Downlighter 15W	2,150/-
Surface Mount+ LED Surface Downlighter 22 W	3,495/-
3W Linea Sharp	1,390/-
6W Linea Sharp	2,060/-
10W Linea Sharp	3,190/-
20W Linea Sharp	7,970/-
30W Linea Sharp	10,150/-
<b>DECORATIVE FANS</b>	
929002597001 Lumin Air Ceiling Fan Crystal	20,999/-
929002597002 Lumin Air Ceiling Fan Silver	20,999/-
<b>COVE LIGHTING</b>	
Linea LED Strip Light Bright 28W with Driver	2,700/-
Linea LED Strip Light Premium 50W with Driver	3,865/-
Linea LED Strip Light Blue 25W with Driver	2,980/-
Pro Glow LED Strip Light 45W with Driver	3,300/-
581919 Nixon Wall Light - Single	Coming Soon
581919 Nixon Wall Light - Single	Coming Soon
581920 Nixon Wall light - Double	Coming Soon
<b>SPOTLIGHT</b>	
56240/31 Star Wall Single Spot 4W	2,300/-
50230/17/E7 Burlap Nickel Wall Single Spot 40W	1,350/-
581879 Aspire	2,399/-
581880 Aspire	3,599/-
581881 Vista	3,599/-
<b>BATHROOM</b>	
581922 Atom Wall Light	Coming Soon

Product Descriptions	MRP
581915 Poise Wall Light	Coming Soon
581918 Majesty	Coming Soon
34034/14/86 Jojoba Wall Lamp Silver 1x7.5W	3,770/-
58157 Aquila LED Wall Light 3000K	3,770/-
58158 Aquila LED Wall Light 3000K	4,400/-
31165 Mirror LED Wall Light 11W	2,436/-
31167 Mirror LED Wall Light 11W	2,900/-
<b>TRACK LIGHT</b>	
31445 Track Light Stanchion Track 10W Head	3,850/-
31446 Track Light Stanchion Track 20W Head	4,550/-
31447 Track Light Stanchion Track 30W Head	5,750/-
31448 Track Light Stanchion Track GU10 Head	2,050/-
<b>OUTDOOR</b>	
1739193PO Samondra Wall Lantern Anthracite 1x12W	3,200/-
1739030PO Actea Wall Lantern Black 1x12W 176V	3,200/-
1739330PO Petronia Wall Lantern Anthracite 1x12W	3,200/-
1739330PO Drosera Wall Lantern Black 1x12W 176V	3,200/-
1738393PN Kiskadee Wall Lantern Anthracite 1x42W	3,000/-
1738930PN Serres Wall Lantern Black 1x42W 230V	3,000/-
1738030PN Astilbe Wall Lantern Black 1x42W 230V	3,000/-
1738130PN Cormorant Wall Lantern Black 1x42W 230V	3,000/-
17303/47 Macaw Wall Lantern LED Inox 1x3.5W	2,088/-
17302/30 Caiques Wall Lantern LED Black 1x3.5W	1,972/-
17304/30 Eagle Wall Lantern LED Black 1x3.5W	1,856/-
58159 Gamma 2W Single Head LED Wall Light	2,500/-
58160 Gamma 4W Double Head LED Wall Light	3,250/-
58161 Gamma 7W, Three Head LED Wall Light	3,950/-
58162 Alpha 12W, LED Wall washer	4,200/-
31450 Propulsio Updown Lighter Anthracite	3,250/-
58163 Triangular 9W, LED Wall Light	3,950/-
34153 7W Anthracite LED Wall Washer Light	3,000/-
34153 7W White LED Wall Washer Light	2,900/-
58164 Lima 3W Step light	2,350/-
31436 Andromeda 3W Step Light	2,900/-



Product Descriptions	MRP
31435 Andromeda 5W LED Step Light	2,300/-
30974 Step Light LED 2W	850/-
34151 2W Anthracite LED Step Light	950/-
34152 3W Anthracite LED Step Light	1,300/-
31385 7W Anthracite COB Garden Spike 300	1,550/-
31386 12W Anthracite COB Garden Spike 30	2,150/-
58174 Glide Wall Lantern Black E27	4,450/-
58175 Glide Post Black E27	4,450/-
58176 Glide Pedestal Black E27	6,600/-
58168 Yolo Wall Lantern LED Black 1x9W	4,700/-
58169 Yolo Pedestal LED Black 1x9W	7,100/-
58172 Blade Wall Lantern LED Black 1x9W	4,700/-
58173 Blade Pedestal LED Black 1x9W	7,100/-
58170 Pylon Wall Lantern LED Black 1x9W	4,700/-
58171 Pylon Pedestal LED Black 1x9W	7,100/-
58166 YOB Wall Lantern LED Black 1x5W	4,700/-
58167 YOB Pedestal LED Black 1x8W	7,100/-
15470 Robin Wall Lantern LED Black 1x8W	3,712/-
15472 Robin pedestal LED Black 1x8W 230	4,454/-
15473 Robin Post LED Black 1x8W 230V	5,800/-
16460 Arbour Wall Lantern LED Anthracite	4,060/-
16476 Arbour Pedestal LED Anthracite 1x8W	4,872/-
16463 Arbour Post LED Anthracite 1x8W	6,728/-
IP67 LED Inground Light 3W	1,955/-
IP67 LED Inground Light 5W	2,890/-
Ip65 LED Inground Light 10W	3,850/-
Ip65 LED Surface Light 12W	2,099/-







