



# Downlight

Excelentes benefícios,  
com o melhor custo.



## Especificações

### Luminária LED Embutir

**80**     
CRI 100-240 V 15,000 h No dimerizável

Potência (W)	6	12	18	24
Fluxo luminoso (lm)	400	900	1.300	2.000
Temperatura de cor (K)	3.000/4000/6.500	3.000/4000/6.500	3.000/4000/6.500	3.000/4000/6.500
Tensão	100-240V	100-240V	100-240V	100-240V
IP	IP20	IP20	IP20	IP20
Diâmetro (altura x diâmetro)	20mm x 120mm	20mm x 170mm	20mm x 225mm	20mm x 300mm

### Luminária LED Sobrepor

Potência (W)	12	18	24
Fluxo luminoso (lm)	900	1.300	2.000
Temperatura de cor (K)	3.000/4000/6.500	3.000/4000/6.500	3.000/4000/6.500
Tensão	100-240V	100-240V	100-240V
IP	IP20	IP20	IP20
Diâmetro (altura x diâmetro)	35mm x 170mm	35mm x 225mm	35mm x 300mm